










P/N LEGEND

A1500 WR-S-XP N X X G1 G 00 R
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩ ⑪

- ① Series No.
- ② Connector type: WR=Right angle
- ③ Mounting type: S=SMT
- ④ No. of circuits
- ⑤ N=Halogen Free
- ⑥ Material: L=LCP
- ⑦ Color: N=Natural ; B=Black
- ⑧ Plating code for contacts:
G1=Gold-flash ; T1=Matte Tin-platd
- ⑨ Plating code for solder tabs:
G=Gold-flash ; T=Matte Tin-platd
- ⑩ Option code: 00=Norma/type
- ⑪ Packing code: R=Tape & Reel(Without Cap or Myar)

SPECIFICATIONS


Current Rating: 1A AC,DC
Voltage Rating: 100V AC,DC
Temperature Range: -40°C ~ +105°C
Contact Resistance: 20MΩ Max.
Insulation Resistance: 500MΩ Min.
Withstanding Voltage: 500V AC/minute
Pin Material: Brass
Solder Tabs: Brass

Circuit No.	Dimensions		
	A	B	C
02P	1.50	6.00	3.60
03P	3.00	7.50	5.10
04P	4.50	9.00	6.60
05P	6.00	10.50	8.10
06P	7.50	12.00	9.60
07P	9.00	13.50	11.10
08P	10.50	15.00	12.60
09P	12.00	16.50	14.10
10P	13.50	18.00	15.60
11P	15.00	19.50	17.10
12P	16.50	21.00	18.60
13P	18.00	22.50	20.10



					燦達電子工業股份有限公司		
					JOINT TECH ELECTRONIC IND. CO., LTD.		
					UNIT	SCALE	SHEET
					mm	1 : 1	1 of 2
B0	EN202412261848	2024.12.27	周耀傑	DRAWN BY		APPROVED BY	TITLE: 1.50mm PITCH 90° WAFER-SMT TYPE
A5	EN202210181201	2022.12.16	劉建芳	周傑亮		董正一	
A4	EN1808290001	2018.08.24	周傑亮	2011.09.07		2011.09.07	
A3	EN1602250001	2016.01.21	周傑亮	GENERAL TOLERANCE			
A2	EN1504240004	2015.04.24	周傑亮	X. X±0.25		ANGLE±	
A1	EN1204200112	2012.04.20	陳錦展	X. XX±0.15			
A0	NEW RELEASE	2011.06.16	周傑亮	X. XXX±0.05			
REV.	DESCRIPTION	DATE	NAME				
				DRAW NO. :			
				A1500WR-S-XPXXXXX00X			B0



02~08 Contacts



Unreeling direction →




Number of Contacts	W±0.3	F±0.1	S±0.1	Q'ty/Reel
02P	16	7.50		1,000
03P	16	7.50		1,000
04P	24	11.50		1,000
05P	24	11.50		1,000
06P	24	11.50		1,000
07P	24	11.50		1,000
08P	24	11.50		1,000
09P	32	14.20	28.40	1,000
10P	32	14.20	28.40	1,000
11P	32	14.20	28.40	1,000
12P	32	14.20	28.40	1,000
13P	44	20.20	40.40	1,000




NOTE:

Material: Transparent
Anti-static Polystyrene.

09~13 Contacts



Unreeling direction →



					燦達電子工業股份有限公司 JOINT TECH ELECTRONIC IND. CO., LTD.						
					UNIT	SCALE	SHEET	TITLE:			
B0	EN202412261848	2024.12.27	周耀傑		mm	1 : 1	2 of 2	1.50mm PITCH 90° WAFER-SMT TYPE TAPING SPEC.			
A5	EN202210181201	2022.12.16	劉建芳		DRAWN BY 周傑亮		APPROVED BY 董正一				
A4	EN1808290001	2018.08.24	周傑亮								
A3	EN1602250001	2016.01.21	周傑亮	2011.09.09		2011.09.09					
A2	EN1504240004	2012.04.24	周傑亮	GENERAL TOLERANCE							
A1	EN1204200112	2012.04.20	陳錦展	X. X±0.25		ANGLE±		DRAW NO. : A1500WR-S-XPNNXXXX00X			
A0	NEW RELEASE	2011.09.09	周傑亮	X. XX±0.15							
REV.	DESCRIPTION	DATE	NAME	X. XXX±0.05							
										REV. B0	