

PV9 SERIES ANTI-VANDAL SWITCH

ANTI-VANDAL
SWITCHES

DETECTOR
SWITCHES

DIP
SWITCHES

KEYLOCK
SWITCHES

NAVIGATION
SWITCHES

PUSHBUTTON
SWITCHES

ROCKER
SWITCHES

ROTARY
SWITCHES

SLIDE
SWITCHES

SNAP ACTION
SWITCHES


TACTILE
SWITCHES

TOGGLE
SWITCHES

CAP
OPTIONS




APPLICATIONS / MARKETS




Audio / Visual



Security Devices



Industrial Controls



Kiosks



Electrical Housewares



Medical Equipment

SPECIFICATIONS

Electrical Rating: 2A, 48VDC
Mechanical Life: 1,000,000 Cycles
Electrical Life: 50,000 Cycles
Contact Resistance: 50mΩ Max.
Insulation Resistance: 1000 MΩ Min. @ 500VDC
Dielectric Strength: 2,000VAC
Operating/Storage Temperature: -35°C to 85°C
Travel: 2.8mm
Moisture Protection: IP65
Contact Arrangement: DPST-NO/NC or 4PST-2NO/2NC
Actuation Force: 6.5N
Panel Thickness: 1-10mm for Momentary
1-12mm for Latching
Hex Nut Torque: 0.6Nm

FEATURES & BENEFITS

- 28mm diameter panel cutout
- Dot or ring illumination options available
- Multiple switch functions available
- Multiple illumination voltage options
- IP65 rated
- DPST-NO/NC or 4PST-2NO/2NC
- Soldered wire leads (300mm long) optional

PART NUMBER CONFIGURATOR

Series	Actuator Options	Terminal Options	Function Options	Rating Options	Body Finish Options	Actuator Finish Options	Lens Style Options	LED Color Options	Illumination Voltage Options
PV9	F - Flat	2 - Solder
W - Wire Leads
300mm long	Y -
1P Off-(On) +
1P On-(Off)
T -
1P Off-On +
1P On-Off
V -
2P Off-(On) +
2P On-(Off)
U -
2P Off-On,
2P On-Off	0 - 2A,
48VDC	S - Stainless
Steel
1 - Black
Anodized	S - Stainless
Steel
1 - Black
Anodized	NONE - Non-
Illuminated
2 - Dot
Illumination
3 - Ring
Illumination	NONE- Non-
Illuminated
0 - White
1 - Red
2 - Orange
3 - Green
4 - Blue
5 - Yellow
F - Red/Orange
G - Red/Green
H - Red/Blue
J - Red/Yellow
K - Orange/Green
L - Orange/Blue
M - Orange/Yellow
N - Green/Blue
P - Green/Yellow
R - RGB	NONE - Non-
Illuminated
1 - Base Voltage*
3 - 6V
4 - 12V
5 - 24V
6 - 125V
7 - 250V

NOTES:
() denotes function is momentary
*Base voltage for LED colors red, yellow, and orange is 1.8V @ 20mA
*Base voltage for LED colors blue, green and white is 2.8V @ 20mA

Specifications subject to change without notice 8.25.2025



E-SWITCH®



www.e-switch.com

800.867.2717

1

PV9 SERIES ANTI-VANDAL SWITCH

BODY DIMENSIONS



E-SWITCH®

www.e-switch.com

800.867.2717

2

ANTI-VANDAL
SWITCHES

DETECTOR
SWITCHES

DIP
SWITCHES

KEYLOCK
SWITCHES

NAVIGATION
SWITCHES

PUSHBUTTON
SWITCHES

ROCKER
SWITCHES

ROTARY
SWITCHES

SLIDE
SWITCHES

SNAP ACTION
SWITCHES


TACTILE
SWITCHES

TOGGLE
SWITCHES


CAP
OPTIONS

PV9 SERIES ANTI-VANDAL SWITCH


ACTUATOR OPTIONS




NON-ILLUMINATED





DOT ILLUMINATED



RING ILLUMINATED



SCHEMATICS



E-SWITCH®

www.e-switch.com

800.867.2717



3

PV9 SERIES ANTI-VANDAL SWITCH


STANDARD LED
WIRE LEAD

SWITCH	WIRE	LENGTH
SW1-1a	WIRE, 24AWG AWM UL1015, WHITE	300.0 [11.8 in]
SW1-2a	WIRE, 24AWG AWM UL1015, WHITE	300.0 [11.8 in]
SW1-3a	WIRE, 24AWG AWM UL1015, BLUE	300.0 [11.8 in]
SW1-4a	WIRE, 24AWG AWM UL1015, BLUE	300.0 [11.8 in]
SW1-1b	WIRE, 24AWG AWM UL1015, WHITE	300.0 [11.8 in]
SW1-2b	WIRE, 24AWG AWM UL1015, WHITE	300.0 [11.8 in]
SW1-3b	WIRE, 24AWG AWM UL1015, BLUE	300.0 [11.8 in]
SW1-4b	WIRE, 24AWG AWM UL1015, BLUE	300.0 [11.8 in]
SW1- (+)	WIRE, 24AWG AWM UL1015, RED	300.0 [11.8 in]
SW1- (-)	WIRE, 24AWG AWM UL1015, BLACK	300.0 [11.8 in]

** WIRE LEADS PROVIDED ARE DEPENDANT ON THE FUNCTION AND/OR ILLUMINATION SELECTED **



BOTTOM VIEW
SHOWN WITHOUT
WIRING



PANEL CUTOUT

