



HPX MIRROR MOUNTING TAPE 2500



HPX MIRROR MOUNTING TAPE 2500 is a double-sided polyethylene foam mounting tape developed for permanent applications where good load-bearing capacity is required.

Applications

- Mounting mirrors.
- Fixing profiles and decorative or design elements.
- Mounting signs and decorative panels.
- Fixing badges, hooks, rails, cable ducts, point of sale displays, etc.
- Installation of shelf edge labelling systems.
- Indoor and outdoor use.

Construction

Adhesive	modified acrylic pressure sensitive, high tack
Carrier	polyethylene foam
Liner	white LDPE red, easy to remove

Technical details

Thickness	1,10 mm
Adhesive strength	20 N/25 mm
Service temperature range	-40°C to +120°C
Solvent resistance	good
Chemical resistance	very good
UV resistance	very good
Humidity resistance	very good
Dynamic shear	6 kg/cm ²
Static shear	1 kg/3,23 cm ² for 7 days at 23°C
Density	100 kg/m ³

Art. No.	width	length	colour	Pack.	EAN code
DS1905	19 mm	5 m	white	24	5425014220124
DS1925	19 mm	25 m	white	10	5425014222531

Recommendations for use

Temperature: between +15°C and +30°C. The surface should be clean, dry, free of dust, oil and grease. Avoid touching the adhesive side of the tape during the application to avoid affecting its performance. Apply pressure-sensitive tapes under maximum pressure to achieve the optimum pressure level. The indicated performance level is

The above information is given in good faith, but the user should assure himself that the performance of the product is sufficient for the application. The quoted values are average and should not be taken as maximum or minimum values for specific purposes. Option Tape Specialties cannot be held responsible for product failure unless full testing has been carried out. The customer has to decide on the tape's suitability for the own application.



www.hpx.eu

Frankrijkstraat 8 | Zone Waas nummer 2529 | 9140 Temse - Belgium
Tel. : +32 (0)3 710 19 19 | Fax : +32 (0)3 711 34 64 | info@hpx.eu - www.hpx.eu

Latest version 03/05/2021



HPX MIRROR MOUNTING TAPE 2500

reached after an adhesion time of 24 hours at +23°C.

Storage and shelf life

Clean and dry in a well-ventilated area, preferably at a temperature between +10°C and +30°C. Stored under these conditions, the shelf life will be at least 24 months.

The above information is given in good faith, but the user should assure himself that the performance of the product is sufficient for the application. The quoted values are average and should not be taken as maximum or minimum values for specific purposes. Option Tape Specialties cannot be held responsible for product failure unless full testing has been carried out. The customer has to decide on the tape's suitability for the own application.



www.hpx.eu

Frankrijkstraat 8 | Zone Waas nummer 2529 | 9140 Temse - Belgium
Tel. : +32 (0)3 710 19 19 | Fax : +32 (0)3 711 34 64 | info@hpx.eu - www.hpx.eu

Latest version 03/05/2021