



HPX MASKING TAPE 60°C 4050



HPX MASKING TAPE 60°C 4050 is a masking tape in painting quality for general purposes. Suitable for domestic and industrial use. Temperature resistant up to 60°C.

Applications

- For indoor use.
- Suitable for automotive as well as domestic and industrial use.
- Good adhesion to metal, glass, plastics and rubber.
- Leaves no glue residues during applications up to 60°C.
- Not UV-resistant: for outdoor use, remove within 8 hours after application.

Construction

Adhesive	natural rubber
Carrier	crepe paper cream

Technical details

Thickness	0,13 mm
Adhesive strength	5 N/25 mm
Tensile strength	87,5 N/25 mm
Temperature resistance	+60°C
Short term temperature	+80°C
Solvent resistance	solvent-resistant

Art. No.	width	length	colour	Pack.	EAN code
MA1950	19 mm	50 m	cream	48	8711347173259
MA2550	25 mm	50 m	cream	36	8711347178773
MA3050	30 mm	50 m	cream	40	5425014227871
MA3850	38 mm	50 m	cream	24	8711347179060
MA5050	50 mm	50 m	cream	24	8711347173273

Recommendations for use

Temperature: between +10°C and +35°C. The surface should be clean, dry, free of dust and grease. Avoid touching the adhesive side of the tape during the application to avoid affecting its performance. Apply pressure-sensitive tapes under maximum pressure to achieve the optimum pressure level. The indicated performance level is reached after an adhesion time of 24 hours at +23°C.

Storage and shelf life

Clean and dry in a well-ventilated area, preferably at a temperature between +10°C and +30°C. Stored under these

The above information is given in good faith, but the user should assure himself that the performance of the product is sufficient for the application. The quoted values are average and should not be taken as maximum or minimum values for specific purposes. Option Tape Specialties cannot be held responsible for product failure unless full testing has been carried out. The customer has to decide on the tape's suitability for the own application.



www.hpx.eu

Frankrijkstraat 8 | Zone Waas nummer 2529 | 9140 Temse - Belgium
Tel. : +32 (0)3 710 19 19 | Fax : +32 (0)3 711 34 64 | info@hpx.eu - www.hpx.eu

Latest version 03/05/2021



HPX MASKING TAPE 60°C 4050

conditions, the shelf life will be at least 12 months.

The above information is given in good faith, but the user should assure himself that the performance of the product is sufficient for the application. The quoted values are average and should not be taken as maximum or minimum values for specific purposes. Option Tape Specialties cannot be held responsible for product failure unless full testing has been carried out. The customer has to decide on the tape's suitability for the own application.



www.hpx.eu

Frankrijkstraat 8 | Zone Waas nummer 2529 | 9140 Temse - Belgium
Tel. : +32 (0)3 710 19 19 | Fax : +32 (0)3 711 34 64 | info@hpx.eu - www.hpx.eu

Latest version 03/05/2021