



Product: 9501 ☑

RS-232, #24-1pr, SR-PVC, O/A Foil, PVC Jkt, CMG, 75Ω

Product Description

Computer EIA RS-232 Cable, 24 AWG stranded (7x32) tinned copper conductors, semi-rigid PVC insulation, 1 twisted pair, overall Beldfoil® shield (100% coverage), 24 AWG stranded tinned copper drain wire, PVC jacket.

Technical Specifications

Product Overview

Suitable Applications:	RS-232 Applications; Computer Communications; Low Voltage Analog Signals (4-20ma, 0-10v,); Low Voltage Digital Control (24v,); Line Level Audio; Panel Wiring

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Pair(s)	1	24 AWG	7x32	TC - Tinned Copper

Insulation

Elemei	nt Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Pair(s)	SR-PVC - Polyvinyl Chloride (Semi-Rigid)	0.011 in (0.28 mm)	0.044 in (1.1 mm)	Black & Red

Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	24 AWG (7x32) TC

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.032 in (0.81 mm)	0.156 in (3.96 mm)
Overall Cable Diameter (Nominal): 0.1	156 in (3.96 mm)

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR		Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Inductance	Nom. Velocity of Prop.	Max. Current
Pair(s)	24 Ohm/1000ft	40 pF/ft	t (130 pF/m)	74 pF/ft (240 pF/m)	0.19 μH/ft (0.62 μH/m)	60%	2.2 Amps per Conductor at 25°C
Nom Outer Shield DCR@Cond DCR1-cnv: 18 Ohm/1000ft (59 Ohm/km)							

High Frequency (Nominal/Typical)

Nom. Insertion Loss (Attenuation)
11.6 dB/100m
11.6 dB/100m

Voltage

UL Voltage Rating 300 V (CMG), 300 V (UL AWM 2464)

Mechanical Characteristics

Temperature

UL Temperature	Operating
80°C	-30°C to +80°C

Bend Radius

Stationary Min.	Installation Min.
1.6 in (41 mm)	1.6 in (41 mm)

Max. Pull Tension:	17 lbs (7.7 kg)
Bulk Cable Weight:	12 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor (Not Riser or Plenum), Indoor
Flammability / Reaction to Fire:	UL 1685 FT4 Loading, FT4, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca; CPR UKCA Class: Eca
NEC / UL Compliance:	Article 800, CMG
AWM Compliance:	AWM 2464, AWM I/II A
CEC / C(UL) Compliance:	CMG, LL7874
European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Plenum Number:	88641, 82641

History

Undate and Revision:	Revision Number: 0.537 Revision Date: 09-07-2025
Update and Revision:	Revision Number, 0.557 Revision Date, 09-07-2025

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC/EAN	Footnote
9501.0030	Chrome	Reel	30 m	8719605020741	
9501 060100	Chrome	Reel	100 ft	612825254065	
9501.00U152	Chrome	UnReel	152 m	8719605020758	
9501.01152	Chrome	Reel	152 m	8719605020772	
9501.00U305	Chrome	UnReel	305 m	8719605020765	
9501.01305	Chrome	Reel	305 m	8719605020789	
9501 060500	Chrome	Reel	500 ft	612825254096	
9501 060U500	Chrome	UnReel	500 ft	612825254058	
9501 0601000	Chrome	Reel	1,000 ft	612825254072	С
9501 060U1000	Chrome	UnReel	1,000 ft	612825254041	
9501 0605000	Chrome	Reel	5,000 ft	612825254102	
9501 06010000	Chrome	Reel	10,000 ft	612825254089	С

Footnote: C - CRATE REEL PUT-UP.

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.