


5					6					7					8				
COUNT	DESCRIPTION OF REVISIONS				BY	CHKD	DATE			COUNT	DESCRIPTION OF REVISIONS				BY	CHKD	DATE		
△							..			△							..		
△							..			△							..		
△							..			△							..		



NOTE: 1 APPLICABLE CRIMPING CONTACT : HR22-SC-222(CL122-0008-8)
(APPLICABLE WIRE : AWG#24~28, OUTER DIMENSION OF JACKET: φ 1.15MAX)
APPLICABLE CONTACT EXTRACTION TOOL : RP6-SC-TP(CL150-0039-0)
2 ACROSS FLATS OF HEXAGON SOCKET OF REF.NO. ⑩ , ⑫ : 1.27.
3 THE RECOMMENDED CLAMP TORQUE OF REF.NO. ⑧ : 2 N · m.
LOCTITE 271 , LOCTITE OR EQUIVALENT IS RECOMMENDED TO PREVENT REF.NO. ⑧ FROM LOOSENING.
4 THE RECOMMENDED CLAMP TORQUE OF REF.NO. ⑩ , ⑫ : 0.3 TO 0.4 N · m.
5 ROTATION EXAMPLES OF REF.NO. ① AND ⑧ ARE SHOWN.

6	PHOSPHOR BRONZE	NICKEL PLATING	12	STEEL	NICKEL PLATING M2.6x0.45x3
5	STEEL	ZINC CHROMATED	11	BRASS	
4	BRASS	NICKEL PLATING	10	STEEL	NICKEL PLATING M2.6x0.45x2
3	SIR	(BLACK)	9	NBR	(BLACK)
2	PBT	(BLACK) UL94V-0	8	BRASS	NICKEL PLATING
1	ZINC ALLOY	NICKEL PLATING	7	SIR	(BLACK)
NO.	MATERIAL	FINISH, REMARKS	NO.	MATERIAL	FINISH, REMARKS

CODE NO. (OLD)		DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
		J. Komatsu	J. Komatsu	E. Kunita	M. Sato	
		06.03.17	06.03.17	06.03.18	06.03.20	

	DRAWING NO.	PART NO.
	EDC3-043648-73	HR22-12TPD-20SC(73)
	SCALE 2 : 1	CODE NO. CL122-0010-0-73
UNITS mm	HIROSE ELECTRIC CO., LTD.	