


SKINTOP® MS-XL

SKINTOP® MS-XL, brass cable gland with wide, variable clamping ranges, with long connection thread especially for thick walls



Variety of approval certifications



Temperature-resistant



Robust



Optimum strain relief



Mechanical resistance



Good chemical resistance

Benefits

Especially for thick walls

Maximum reliability

Wide, variable clamping ranges

Optimum strain relief

Application range

With long connection thread for applications involving a thicker wall.

Product Make-up

PG connection thread acc. to DIN 40430

Last Update (06.04.2018)

©2018 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SKINTOP® MS-XL

Note

Counter nut to be used: SKINDICHT® SM

Refer to SKINTOP® PG accessories for suitable accessories

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000441 ETIM 5.0 Class-Description: Cable screw gland
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000441 ETIM 6.0 Class-Description: Cable screw gland
Caution:	Refer to Appendix T21 for the installation dimensions and torques
Material:	Body: nickel-plated brass Insert: polyamide Sealing: CR O-ring: NBR
Protection rating:	IP 68 - 10 bar
Temperature range:	dynamic -25°C up to + 100°C static -40°C up to +100°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

**SKINTOP® MS-XL**

Article number	Article designation / size	Clamping range ØF (mm)	SW wrench size mm	Overall length, C (mm)	Thread length, D (mm)
SKINTOP® MS-XL					
52115700	PG 7	2 - 6.5	14	32	12
52115710	PG 9	4 - 8	17	35	12
52115720	PG 11	4 - 10	20	38	12
52115730	PG 13,5	5 - 12	22	39.5	12
52115740	PG 16	8 - 14	24	40.5	12
52115750	PG 21	11 - 18	30	45	12
52115760	PG 29	16 - 25	40	52	15

Last Update (06.04.2018)

©2018 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16