

SKINDICHT® SM-PE-M

SKINDICHT® SM-PE-M, counter nuts with cutting edges to cut through the insulating layer, thus guaranteeing an optimum EMC contact



Mechanical resistance



Good chemical resistance

Benefits

Cutting edges cut through the insulating layer, thus guaranteeing an optimum EMC contact
Suitable for all metric glands used in earthing and EMC applications

Application range

For lacquered, anodised or powder-coated housings.

Product Make-up

Metric connection thread acc. to DIN EN 60423
Basis for technical information DIN IEC 62444

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000940

ETIM 5.0 Class-Description: Locknut for cable screw gland

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000940

ETIM 6.0 Class-Description: Locknut for cable screw gland

Material:

Nickel-plated brass

Temperature range:

-60°C to +200°C

SKINDICHT® SM-PE-M**Note**

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.



SKINDICHT® SM-PE-M

Article number	Article designation / size	Thickness (mm)	SW wrench size mm	Outer Ø (mm)
SKINDICHT® SM-PE-M				
52103300	M 12 x 1,5	4.7	15	17.3
52103310	M 16 x 1,5	4.7	19	21.9
52103320	M 20 x 1,5	4.7	24	27.7
52103330	M 25 x 1,5	5.2	30	34.6
52103340	M 32 x 1,5	5.7	36	41.5
52103350	M 40 x 1,5	6.5	46	53.1
52103360	M 50 x 1,5	6.5	60	69.3
52103370	M 63 x 1,5	7.0	70	80.8
52103371	M 75 x 1,5	8.0	85	95.0
52103372	M 90 x 2	10.0	102	114.0
52103373	M 110 x 2	12.0	124	135.0

Last Update (10.04.2018)

©2018 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16