


KEMET Part Number: A765EB107M1CLAE025
(KCS016M101SMD6.3LA5.7)

Polymer Aluminum, 105C LowZ, KEMET, A765, 100 uF, 20%, 16 V, -55/+105C



Dimensions

D	6.3mm +/-0.5mm
L	5.7mm +/-0.3mm
W	0.5mm +0.3mm
A	6.6mm +/-0.2mm
B	6.6mm +/-0.2mm
C	7.3mm +/-0.2mm
E	2.6mm NOM
P	2.1mm NOM

Packaging Specifications

Packaging:	T&R, 380mm
Packaging Quantity:	1000

General Information

Dielectric:	Polymer Aluminum
Style:	SMD Can
Supplier:	KEMET
Series:	A765
Description:	Surface Mount, Polymer Aluminum
RoHS:	Yes
Lead:	V-Chip

Specifications

Capacitance:	100 uF
Capacitance Tolerance:	20%
Voltage DC:	16 VDC, 18.4 VDC (Surge)
Temperature Range:	-55/+105C
Rated Temperature:	105C
Life:	2000 Hrs
Resistance:	25 mOhms (100kHz 20C)
Current:	2500 mAmps (100kHz 105C)
Impedance Ratio at -25C:	1.25
Impedance Ratio at -55C:	1.25