

LARISA-WW-CLIP16

~55° wide beam. Clip fastening for 1.6 mm thick PCB


TECHNICAL SPECIFICATIONS:

Dimensions	10.0 mm
Height	7.5 mm
Fastening	glue, clips
Colour	black
Box size	
Box weight	0 kg
Quantity in Box	10000 pcs
ROHS compliant	yes ⓘ



MATERIAL SPECIFICATIONS:



Component	Type	Material	Colour
LARISA-WW	Single lens	PMMA	clear
LARISA-HOLDER-CLIP16	Holder	PC	black





PHOTOMETRIC DATA (MEASURED):





LED XB-D
FWHM 57.0°
Efficiency 84 %
Peak intensity 0.900 cd/lm
LEDs/each optic 1
Light colour White
Required components:





LED XD16
FWHM 50.0°
Efficiency 79 %
Peak intensity 1.000 cd/lm
LEDs/each optic 1
Light colour White
Required components:



LED LUXEON A
FWHM 70.0°
Efficiency 85 %
Peak intensity 0.700 cd/lm
LEDs/each optic 1
Light colour White
Required components:





LED LUXEON Rebel
FWHM 62.0°
Efficiency 88 %
Peak intensity 0.900 cd/lm
LEDs/each optic 1
Light colour White
Required components:





PHOTOMETRIC DATA (MEASURED):





LED LUXEON Rebel ES
 FWHM 60.0°
 Efficiency 86 %
 Peak intensity 0.900 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:





LED NCSxx19A
 FWHM 52.0°
 Efficiency 83 %
 Peak intensity 1.000 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:



LED NVSxx19A
 FWHM 57.0°
 Efficiency 82 %
 Peak intensity 0.900 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:





LED Duris S5 (2 chip)
 FWHM 50.0°
 Efficiency 86 %
 Peak intensity 1.200 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:



PHOTOMETRIC DATA (MEASURED):

OSRAM
Opto Semiconductors

LED Oslon SSL 80
FWHM 66.0°
Efficiency 84 %
Peak intensity 0.900 cd/lm
LEDs/each optic 1
Light colour White
Required components:



GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDiL Oy

Joensuunkatu 13
FI-24240 SALO
Finland

LEDiL Inc.

228 West Page Street
Suite D
Sycamore IL 60178
USA

Local sales and technical support

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)

Shipping locations

Salu, Finland
Hong Kong, China

Distribution Partners

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)