

ROCKER SWITCHES

PRODUCT NUMBER 1911.1102



TECHNICAL DATA

Product number	1911.1102	
Business unit	Switches, Sensors & Controls	
Product Manager	Heinichen	
Product family	Rocker switches	
Actuation type	direct	
Packing unit	300	
Weight	3.200 g	
ROHS conform	yes	
Output	catalog before 2009 / Web-Shop / catalog	
Switching function	ON / OFF switch (SPST)	
Material fixed contact	Cu silver-plated	
Number of poles	1 - pole	
connections	Quick-connect terminal, 4.8 x 0.8	
Mechanical life endurance	75E3	
Rating IEC	6 (2) A 250 V AC 4 (1) A 250 V AC 5E4	
Contact resistance (new condition)	< 100 (1 A 12 V DC) mOhm	
Insulation resistance (new condition)	> 100 (500 V DC) MOhm	
Voltage strength at 250 V	→ function insulation / basic insulation	1 500 V
	→ reinforced insulation	3 000 V
	→ small contact distance	500 V
Proof tracking	250 PTI	
Insulation spacing	acc. to EN 61058 for reinforced or double insulation	
Protection type	→ Connection	IP 40
	→ Actuator	IP 40
Ambient temperature	-20 °C ... +85 °C	
Ambient temperature	-20 °C ... +55 °C	
Storage temperature	-40 °C ... +80 °C	
Flammability	UL 94 V-0	
Glow wire test temperature	850 °C	
Actuators and additional actuators	rocker: PA, black	

Housing description	housing: PA, black	
Connection surface	→ bearing connection → external connection	silver plated silver plated
Contact material	Ag	
Contact distance	≥ 3 mm	
Contact type	lifting contact	
Plug force of the terminals	≤ 80 N	
Operating force	2 - 5 N	
Approval marks	cULus / ENEC 05	
Suitable for appliances of protection class	II	
EN 60335 cap. 30 conform "G"	yes	
Type of fastening	Snap fastening	
Degree of pollution	3	
Stock version	●	

Technical changes reserved. Dimensions are not binding.

Detailed specifications available on request.

Marquardt GmbH · Schloss-Straße 16 · 78604 Rietheim-Weilheim · Germany
 Phone: +49 (0) 7424 / 99-0 · Fax: +49 (0) 7424 / 99-2399 · www.marquardt.com · marquardt@marquardt.de