

BN 200

Einpressmuttern

Stahl einsatzgehärtet 550-650 HV


verzinkt-blau


ISO 4042


Verbindungselemente Härte ≥ 320 HV mit galvanischen Überzügen: Wasserstoffversprödungsgefahr! Weitere Hinweise zu den Restgefahren finden Sie in der


Einleitung.











Article# ~	d1 -	d2 max -	d3 -	k -	a min.	Bohr-Duchm. +0,08/ -	S +	h max.
1098101	M2	4.22	6.3	1.5	4.8	4.25	1.1-1.4	0.97
1098152	M2.5	4.22	6.3	1.5	4.8	4.25	1.1-1.4	0.97
1098195	M3	4.72	7.1	1.75	5.6	4.75	1.1-1.4	0.97
1098284	M4	5.36	7.9	2.4	6.9	5.4	1.1-1.4	0.97
1098322	M5	6.38	8.7	2.4	7.1	6.4	1.1-1.4	0.97
1098357	M6	8.68	11.1	4.4	8.6	8.75	1.4-2.3	1.38
1098381	M8	10.44	12.7	6	9.7	10.5	1.4-2.3	1.38