

H

G

F

E

D

C

B

A

REVISION RECORD			
REV	ECN	DESCRIPTION	DRFT

H

G

F

E

D

C

B

A

Technical characteristics:

Specifications

DIN EN 60 664-1
DIN EN 61 984




Inserts

01. Number of contacts :10+PE
02. Rated Current :16A
03. Rated Voltage :500V
04. Pollution degree :3
05. Rated impulse voltage :6kv¹⁰
06. Insulation resistance : $\geq 10 \Omega$
07. Material:Polycarbonate
08. Rated voltage acc. to UL/CSA:600V
09. Limiting temperatures : $-40^{\circ}\text{C}\sim+125^{\circ}\text{C}$
10. Flammability acc. to UL94:V0
11. Mechanical working life
(mating cycles) : ≥ 500

Contacts

01. Material:Copper alloy
02. Surface:hard-silver plated
03. Contact resistance : $\leq 1\text{m}\Omega$
04. Terminal :Crimp terminal
05. Wire gauge :0.14-4.0mm² (AWG 26-12)
06. Stripping length :7.5mm
07. Rohs Compliance

Note:Crimp contact pins should
order separately



PART NO.: /		 DEGSON® NINGBO DEGSON ELECTRICAL CO., LTD	
APPD: HJS 2016.10.8		NAME: DEE-010-FC	
CHKD: JY 2016.10.8			
DRFT: Mr:Yang 2016.09.25		TITLE: CUSTOMER DRAWING	
		DRAWING NO.: DEE-010-FC-E01	
		DO NOT SCALE	
THIRD ANGLE PROJECTION		SCALE 1:1	
3		1	

8

7

6

5

4

3

2

1