

Flat suction cup (round)

PFYN 20 SI-55 G1/8-AG

Part no.:10.01.01.00156

<https://www.schmalz.com/10.01.01.00156>

Homepage > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat suction cup (round) > Flat Suction

Cups PFYN > PFYN 20 SI-55 G1/8-AG

Flat suction cup (round) for smooth or slightly rough surfaces



Size: 20

Suction cup material: Silicone SI

Material hardness: 55 °Sh


Material characteristics:

FDA-compatible

Nipple material: Aluminium

Vacuum connection: G1/8"-M

Design Data



Attribute	Value
dn	2 mm
Dmax(S)	23 mm
Ds	20 mm
G1	G1/8"-AG
H	15 mm
LG1	8 mm
SW1	14 mm
Z (Stroke)	2.2 mm

Technical Data

Flat suction cup (round)

PFYN 20 SI-55 G1/8-AG

Part no.:10.01.01.00156


<https://www.schmalz.com/10.01.01.00156>



Attribute	Value
Suction force (-600mbar)	15.5 N
Volume	0.8 cm ³
Curve radius (min) (convex)	20 mm
Hose diameter (empf.) d	4 mm
Size	20
Number of folds	0
Suction cup material	Silicone SI
Material hardness [Shore A]	55 Shore A
Weight	5.6 g
Product family	PFYN

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a smooth, dry workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Spare Parts



SA-NIP N006 G1/8-AG DN200

Part no.10.01.01.03530

Suction cup connection nipple

Nipple: N 006

Thread G1: G1/8"-M

Overall length: 19.5 mm

Fitting length: 5 mm

Nominal size: 2.00 mm

Material: Aluminium

Flat suction cup (round)

PFYN 20 SI-55 G1/8-AG

Part no.:10.01.01.00156

<https://www.schmalz.com/10.01.01.00156>



PFG 20 SI-55 N006

Part no.10.01.01.00032

Flat suction cup (round) for smooth or slightly rough surfaces

Size: 20

Suction cup material: Silicone SI

Material hardness: 55 °Sh

Material characteristics:

FDA-compatible