

Spring plunger

FSTE G1/2-AG 25

Part no.:10.01.02.00574

<https://www.schmalz.com/10.01.02.00574>



Homepage > Vacuum Technology for Automation > Vacuum Components > Mounting Elements > Spring plunger > Spring Plungers FSTE > FSTE G1/2-AG 25

Spring plunger with damping and height compensation




Suction cup connection: G1/2"-M

Vacuum connection: G3/8"-F

Spring stroke Z: 25 mm

Design Data



Attribute	Value
G1	G3/8"-IG
G2	G1/2"-M
G3	M30x1.5-M
H	105.5 mm
H2	42.5 mm
LG1	13 mm
LG2	10.5 mm
LG3	55 mm
SW1	36 mm
SW2	24 mm
SW3	24 mm
Z (Stroke)	25 mm

Spring plunger

FSTE G1/2-AG 25

Part no.:10.01.02.00574

<https://www.schmalz.com/10.01.02.00574>




Technical Data

Attribute	Value
Spring rate	3.829 N/mm
Spring pretension	25.64 N
Spring force, center	73.5 N
Vertical load	4,900 N
Horizontal load	1,870 N
Weight	400 g
Operating temperature	0 ... 80 °C

Note: Spring force: Referred to 50% of operating stroke Static loading: Maximum static loading
Horizontal stress: The specification of the horizontal stress refers to the lower edge of the plunger with extended spring. It is a maximum static stress and it impairs the spring compression and extension in horizontal position

Spare Parts



DRUCK-FED 2x23 40.5 3.828

Part no.20.08.02.00095

Pressure spring

Wire size: 2 mm

Diameter: 23 mm

Length L: 40.5 mm

Spring rate: 3.828 N/mm

Accessories

[Contact to Schmalz](#)

Schmalz Sp.z.o.o. | Kobaltowa 4, 62-002 Złotniki, Polen | +48 22 460 49 70 | schmalz@schmalz.pl

Page 2 of 8

Spring plunger

FSTE G1/2-AG 25

Part no.:10.01.02.00574

<https://www.schmalz.com/10.01.02.00574>



FLK G1/2-IG G1/2-AG

Part no.10.01.03.00175

Flexible suction cup mounting for adaptation to sloping surfaces

Thread G1: G1/2"-F

Thread G2: G1/2"-M

Ambient temperature: 0 ... 70 °C



FLK G1/2-IG G1/2-AG V

Part no.10.01.03.00207

Flexible suction cup mounting for adaptation to sloping surfaces

Thread G1: G1/2"-F

Thread G2: G1/2"-M

Shape: Reinforced

Ambient temperature: 0 ... 70 °C



KGL G1/2-IG G1/2-AG

Part no.10.01.03.00111

Suction cup mounting with joint for adaptation to sloping surfaces

Thread G1: G1/2"-F

Thread G2: G1/2"-M


Height H: 40 mm

Spring plunger

FSTE G1/2-AG 25

Part no.:10.01.02.00574

<https://www.schmalz.com/10.01.02.00574>



HTR-STA 62 1N D30 WI

Part no.10.08.03.00148

Holder for flexible mounting of suction cups/spring plungers on sections

Length L: 62 mm

Cross-beam connection: Sliding block

Suction cup or spring plunger conn.:

Contour D30-G1/2

Shape: angled



HTR-ST5 40x40 D30 WI

Part no.10.08.03.00090

Holder for flexible mounting of suction cups/spring plungers on square tubes

Cross-beam connection: 40x40

Suction cup or spring plunger conn.:

Contour D30-G1/2

Shape: angled



HTR-ST5 50x50 D30 WI

Part no.10.08.03.00091

Holder for flexible mounting of suction cups/spring plungers on square tubes

Cross-beam connection: 50x50

Suction cup or spring plunger conn.:

Contour D30-G1/2

Shape: angled

Spring plunger

FSTE G1/2-AG 25

Part no.:10.01.02.00574

<https://www.schmalz.com/10.01.02.00574>



HTR-ST 60x60 D30 WI

Part no.10.08.03.00092


Holder for flexible mounting of suction cups/spring plungers on square tubes

Cross-beam connection: 60x60

Suction cup or spring plunger conn.:

Contour D30-G1/2

Shape: angled



ST G3/8-AG 9 MS-V

Part no.10.08.03.00159

Hose sleeve

Thread G1: G3/8"-M

Internal hose diameter: 9 mm

Material: Brass

Surface: nickel plated



ST G3/8-AG 13 MS-V

Part no.10.08.03.00160

Hose sleeve

Thread G1: G3/8"-M

Internal hose diameter: 13 mm

Material: Brass

Surface: nickel plated

Spring plunger

FSTE G1/2-AG 25

Part no.:10.01.02.00574

<https://www.schmalz.com/10.01.02.00574>



STV-GE G3/8-AG 8

Part no.10.08.02.00237

Push-in Fitting, straight

Thread G1: G3/8"-M

External hose diameter: 8 mm

Material: Brass

Surface: nickel plated

Ambient temperature: -20 ... 80 °C



STV-GE G3/8-AG 10

Part no.10.08.02.00252

Push-in Fitting, straight

Thread G1: G3/8"-M

External hose diameter: 10 mm

Material: Brass

Surface: nickel plated

Ambient temperature: -20 ... 80 °C



STV-GE G3/8-AG 12

Part no.10.08.02.00209

Push-in Fitting, straight

Thread G1: G3/8"-M

External hose diameter: 12 mm

Material: Brass

Surface: nickel plated

Ambient temperature: -20 ... 80 °C

Spring plunger

FSTE G1/2-AG 25

Part no.:10.01.02.00574

<https://www.schmalz.com/10.01.02.00574>



STV-GE G3/8-AG 14

Part no.10.08.02.00211

Push-in Fitting, straight

Thread G1: G3/8"-M

External hose diameter: 14 mm

Material: Brass

Surface: nickel plated

Ambient temperature: -20 ... 80 °C



STV-W G3/8-AG 8

Part no.10.08.02.00236

Push-in Fitting, swivelling elbow

Thread G1: G3/8"-M

External hose diameter: 8 mm

Material: Brass, nickel-plated

Ambient temperature: -20 ... 80 °C



STV-W G3/8-AG 10

Part no.10.08.02.00255

Push-in Fitting, swivelling elbow

Thread G1: G3/8"-M

External hose diameter: 10 mm

Material: Brass, nickel-plated

Ambient temperature: -20 ... 80 °C

Spring plunger

FSTE G1/2-AG 25

Part no.:10.01.02.00574

<https://www.schmalz.com/10.01.02.00574>



STV-W G3/8-AG 12

Part no.10.08.02.00163

Push-in Fitting, swivelling elbow

Thread G1: G3/8"-M

External hose diameter: 12 mm

Material: Brass, nickel-plated

Ambient temperature: -20 ... 80 °C



STV-WF G3/8-AG 8

Part no.10.08.02.00234

Push-in Fitting, swivelling and lockable

Thread G1: G3/8"-M

External hose diameter: 8 mm

Material: Brass, nickel-plated

Ambient temperature: -10 ... 70 °C



STV-WF G3/8-AG 10

Part no.10.08.02.00259

Push-in Fitting, swivelling and lockable

Thread G1: G3/8"-M

External hose diameter: 10 mm

Material: Brass, nickel-plated

Ambient temperature: -10 ... 70 °C