

Flexolink FLK G1/4-IG G1/4-AG

Part no.:10.01.03.00178

<https://www.schmalz.com/10.01.03.00178>




Homepage > Vacuum Technology for Automation > Vacuum Components > Mounting Elements > Jointed Mountings > Flexolink FLK > FLK G1/4-IG G1/4-AG

Flexible suction cup mounting for adaptation to sloping surfaces



Thread G1: G1/4"-F
Thread G2: G1/4"-M
Ambient temperature: 0 ... 70 °C

Design Data



Attribute	Value
-----------	-------

dn	3 mm
G1	G1/4"-IG
G2	G1/4"-M
L	27 mm
LG1	12 mm
LG2	12 mm
SW1	17 mm
W	12 °

Technical Data

[Contact to Schmalz](#)

Schmalz Sp.z.o.o. | Kobaltowa 4, 62-002 Złotniki, Polen | +48 22 460 49 70 | schmalz@schmalz.pl

Page 1 of 2

Attribute	Value
Bending moment	10 Nm
Vertical load	750 N
Weight	30 g