

		1		2		3		4		5		6		7			
												Signature		Revision History		Date Rev.	
A		RoHS & REACH Compliant														A	
B		DB 9P MALE 6 1 9 5 P1 3000± 50mm A A ① ⑤ ④③② DB 9P FEMALE 1 6 5 9 P2														B	
C																C	
D																D	
E		PIN Assignment P1 P2 1 2 3 4 5 6 7 8 9 Carrier Detect Receive Data Transmit Data Data Terminal Ready System Ground Data Set Ready Request to Send Clear to Send Ring Indicator Shell Drain Shell														E	
F		NOTES: 1.CABLE: NON-UL 28AWG(7/0.125TC)*9C+D(7/0.12TC)+AL/MY OD:5.0± 0.20mm JACKET COLOR: BEIGE 2.CONNECTOR: P1: DB 9P/M,SOLDER,BLUE INSULATION, GOLD PLATED CONTACTS, NICKEL PLATED SHELL P2: DB 9P/F,SOLDER,BLUE INSULATION, GOLD PLATED CONTACTS, NICKEL PLATED SHELL 3.HOOD: MOLDED TYPE,PVC 45P,COLOR:BEIGE 4.INSIDE MOLDING: TRANSPARENT PE. 5.THUMB SCREW: #4-40 UNC, MOLDED TYPE,PVC 45P,COLOR:BEIGE 6.ELECTRICLE TEST: (1)100% OPEN SHORT & MIS WIRE TEST. (2)CONTACT RESISTANCE 3 ohm Max . (3)INSULATION RESISTANCE 10M ohm Min . (4)HI-POT TEST:DC 300V/10ms Cross Section: AL-Mylar Conductor Jacket Drain Insulation A-A														F	
G		Drawn by JAN,09,2017 LYD Checked by Approved by 11Jan,2017 Joe ASSMANN Electronic GmbH Part No. AK-610203-030-E EAN:4016032301479 Title DB 9P/M - DB 9P/F CABLE Scale N/A Sheet Unit MM 1/2														G	
H																H	
		1		2		3		4		5		6		7			

	1	2	3	4	5	6	7														
						Signature	Revision History	Date	Rev.												
A	Package Details					RoHS & REACH Compliant			A												
B	Single Cable					Single Cable			B												
	<table><tr><th>P/N</th><th>Cable Length</th><th>Rolling Size (Single Cable)</th><th>Polybag Type (Single Cable)</th><th>Bag Size (Single Cable)</th><th>Article Weight (Single Cable)</th></tr><tr><td>AK-610203-030-E</td><td>3m</td><td>130mm max.</td><td>Ordinary Polybag (Heat Sealed)</td><td>280*150*0.05mm</td><td>0.175kg</td></tr></table>					P/N	Cable Length	Rolling Size (Single Cable)	Polybag Type (Single Cable)	Bag Size (Single Cable)	Article Weight (Single Cable)	AK-610203-030-E	3m	130mm max.	Ordinary Polybag (Heat Sealed)	280*150*0.05mm	0.175kg				
P/N	Cable Length	Rolling Size (Single Cable)	Polybag Type (Single Cable)	Bag Size (Single Cable)	Article Weight (Single Cable)																
AK-610203-030-E	3m	130mm max.	Ordinary Polybag (Heat Sealed)	280*150*0.05mm	0.175kg																
C	Inner Packing Unit					Inner Packing Unit			C												
	<table><tr><th>P/N</th><th>Cable Length</th><th>Quantity (Inner Packing Unit)</th><th>Type (Inner Packing Unit)</th><th>Size (Inner Packing Unit)</th><th>Weight (Inner Packing Unit)</th></tr><tr><td>AK-610203-030-E</td><td>3m</td><td>10 pcs</td><td>Polybag (Heat Sealed)</td><td>380*360*0.05mm</td><td>1.685kg</td></tr></table>					P/N	Cable Length	Quantity (Inner Packing Unit)	Type (Inner Packing Unit)	Size (Inner Packing Unit)	Weight (Inner Packing Unit)	AK-610203-030-E	3m	10 pcs	Polybag (Heat Sealed)	380*360*0.05mm	1.685kg				
P/N	Cable Length	Quantity (Inner Packing Unit)	Type (Inner Packing Unit)	Size (Inner Packing Unit)	Weight (Inner Packing Unit)																
AK-610203-030-E	3m	10 pcs	Polybag (Heat Sealed)	380*360*0.05mm	1.685kg																
D	CARTON DETAILS								D												
	<table><tr><th>P/N</th><th>Cable Length</th><th>Quantity (Carton)</th><th>Measurement (Carton)</th><th>N.W. (Carton)</th><th>G.W. (Carton)</th></tr><tr><td>AK-610203-030-E</td><td>3m</td><td>50pcs</td><td>40*30*20 cm</td><td>8.8kg</td><td>9.5kg</td></tr></table>					P/N	Cable Length	Quantity (Carton)	Measurement (Carton)	N.W. (Carton)	G.W. (Carton)	AK-610203-030-E	3m	50pcs	40*30*20 cm	8.8kg	9.5kg				
P/N	Cable Length	Quantity (Carton)	Measurement (Carton)	N.W. (Carton)	G.W. (Carton)																
AK-610203-030-E	3m	50pcs	40*30*20 cm	8.8kg	9.5kg																
E									E												
F									F												
G						Part No. AK-610203-030-E EAN:4016032301479			G												
H	* "ROTTERDAM" is for Sea Freight shipment * "COLOGNE" is for Air Freight shipment * "LUDENSCHIED" is for Fedex or UPS shipment					Title DB 9P/M - DB 9P/F CABLE Scale Unit N/A MM Sheet 2/2			H												
	1	2	3	4	5	6	7														