

Flexolink FLK G1/4-IG M10x1.25-AG

Part no.:10.01.03.00206

<https://www.schmalz.com/10.01.03.00206>




Homepage > Vacuum Technology for Automation > Vacuum Components > Mounting Elements > Jointed Mountings > Flexolink FLK > FLK G1/4-IG M10x1.25-AG

Flexible suction cup mounting for adaptation to sloping surfaces



Thread G1: G1/4"-F
Thread G2: M10x1.25-M
Ambient temperature: 0 ... 70 °C

Design Data



Attribute	Value
dn	2.8 mm
G1	G1/4"-IG
G2	M10x1.25-M
L	32 mm
LG1	10.5 mm
LG2	8 mm
SW1	17 mm
W	12 °

Technical Data

[Contact to Schmalz](#)

Schmalz Sp.z.o.o. | Kobaltowa 4, 62-002 Złotniki, Polen | +48 22 460 49 70 | schmalz@schmalz.pl

Page 1 of 2

Flexolink

FLK G1/4-IG M10x1.25-AG

Part no.:10.01.03.00206

<https://www.schmalz.com/10.01.03.00206>



Attribute	Value
Bending moment	8 Nm
Vertical load	500 N
Weight	26 g
