

Flexolink FLK G1/2-AG G1/2-AG

Part no.:10.01.03.00153

<https://www.schmalz.com/10.01.03.00153>




Homepage > Vacuum Technology for Automation > Vacuum Components > Mounting Elements > Jointed Mountings > Flexolink FLK > FLK G1/2-AG G1/2-AG

Flexible suction cup mounting for adaptation to sloping surfaces



Thread G1: G1/2"-M
Thread G2: G1/2"-M
Ambient temperature: 0 ... 70 °C

Design Data



Attribute	Value
dn	5.5 mm
G1	G1/2"-AG
G2	G1/2"-M
L	21 mm
LG1	14 mm
LG2	14 mm
SW1	27 mm
W	12 °

Technical Data

Attribute	Value
Bending moment	65 Nm
Vertical load	3,000 N
Weight	100 g