

Flexolink FLK G1/2-IG G1/2-AG

Part no.:10.01.03.00175

<https://www.schmalz.com/10.01.03.00175>



Homepage > Vacuum Technology for Automation > Vacuum Components > Mounting Elements > Jointed Mountings > Flexolink FLK > FLK G1/2-IG G1/2-AG

Flexible suction cup mounting for adaptation to sloping surfaces




Thread G1: G1/2"-F

Thread G2: G1/2"-M

Ambient temperature: 0 ... 70 °C

Design Data



Attribute	Value
-----------	-------

dn	6 mm
----	------

G1	G1/2"-IG
----	----------

G2	G1/2"-M
----	---------

L	33.5 mm
---	---------

LG1	14 mm
-----	-------

LG2	14 mm
-----	-------

SW1	27 mm
-----	-------

W	12 °
---	------

Technical Data

[Contact to Schmalz](#)

Schmalz Sp.z.o.o. | Kobaltowa 4, 62-002 Złotniki, Polen | +48 22 460 49 70 | schmalz@schmalz.pl

Page 1 of 2

Attribute	Value
Bending moment	50 Nm
Vertical load	3,000 N
Weight	100 g