

Bell suction cup (round)

FSGA 14 HT1-60 G1/8-AG

Part no.:10.01.06.00932

<https://www.schmalz.com/10.01.06.00932>



Homepage > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Bellows Suction Cups (Round) > Bellows

Suction Cups FSGA (1.5 Folds) > FSGA 14 HT1-60 G1/8-AG

Bellows suction cup (round) with optimal adaptation to uneven surfaces



Size: 14

Number of folds: 1.5

Suction cup material:

High temp material HT1


Material hardness: 60 °Sh

Material property: imprint-free

Nipple material: Aluminium

Vacuum connection: G1/8"-M

Design Data



Attribute	Value
-----------	-------

d2	5 mm
----	------

Dmax(S)	14.5 mm
---------	---------

dn	3.5 mm
----	--------

Ds	12.5 mm
----	---------

G1	G1/8"-AG
----	----------

H	21.5 mm
---	---------

LG1	7.5 mm
-----	--------

SW1	14 mm
-----	-------

Z (Stroke)	5 mm
------------	------

Technical Data

[Contact to Schmalz](#)

Schmalz Sp.z.o.o. | Kobaltowa 4, 62-002 Złotniki, Polen | +48 22 460 49 70 | schmalz@schmalz.pl

Page 1 of 3

Bell suction cup (round)

FSGA 14 HT1-60 G1/8-AG

Part no.:10.01.06.00932


<https://www.schmalz.com/10.01.06.00932>



Attribute	Value
Suction cup material	High temp material HT1
Material hardness [Shore A]	60 Shore A
Size	14
Number of folds	1.5
Connection	G1/8-AG
Curve radius (min) (convex)	15 mm
Volume	0.42 cm ³
Suction force (-600mbar)	1.2 N
Pull-off force	5 N
Hose diameter (empf.) d	4 mm
Weight	4.8 g
Product family	FSGA

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a smooth, dry workpiece surface - they do not include a safety factor Pull-off force: The pull-off force of the versions made of natural rubber is reduced by about 40% Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Spare Parts



SA-NIP N016 G1/8-AG DN350

Part no.10.01.06.05735

Suction cup connection nipple

Nipple: N 016

Thread G1: G1/8"-M

Overall length: 20 mm

Fitting length: 6 mm

Nominal size: 3,50 mm

Material: Aluminium

Bell suction cup (round)

FSGA 14 HT1-60 G1/8-AG

Part no.:10.01.06.00932

<https://www.schmalz.com/10.01.06.00932>



FGA 14 HT1-60 N016

Part no.10.01.06.00868

Bellows suction cup (round) with optimal adaptation to uneven surfaces

Size: 14

Suction cup material:


High temp material HT1

Material hardness: 60 °Sh

Number of folds: 1.5

Material property: imprint-free

Accessories



SPI 14 PEEK

Part no.10.01.06.03282

Suction cup insert for handling of sensitive workpieces without leaving marks

Size: 14

Material: Polyetheretherketon