

Bellows suction cup NBR (round)

SAB 22 NBR-60 G1/4-AG

Part no.:10.01.06.01653

<https://www.schmalz.com/10.01.06.01653>

Homepage > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Sheet Metal >

Bellows Suction Cups SAB (1.5 Folds) > SAB 22 NBR-60 G1/4-AG

Bellows suction cup (round) for very dynamic handling of smooth and oily workpieces



Size: 22

Suction cup material:

Nitrile rubber NBR


Material hardness: 60 °Sh

Vacuum connection: G1/4"-M

Nipple material: Aluminium

Number of folds: 1.5

Design Data



Attribute

Value

dn 3.5 mm

D1 22 mm

Dmax(S) 24 mm

Ds 20.6 mm

G1 G1/4"-AG

H 25 mm

LG1 10 mm

SW1 16 mm

Z (Stroke) 5.8 mm

Bellows suction cup NBR (round)

SAB 22 NBR-60 G1/4-AG

Part no.:10.01.06.01653

<https://www.schmalz.com/10.01.06.01653>



Technical Data

Attribute	Value
Suction force (-600mbar)	16 N
Pull-off force	24 N
Lateral force	18 N
Lateral force (oily surface)	6 N
Volume	2.48 cm ³
Curve radius (min) (convex)	20 mm
Hose diameter (empf.) d	4 mm
Size	22
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	60 Shore A
Weight	7 g
Product family	SAB
Number of folds	1.5

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a smooth, dry workpiece surface - they do not include a safety factor Lateral force: The specified lateral forces are values measured at a vacuum of -0.6 bar with a dry or oily, smooth, flat workpiece surface. Depending on the workpiece surface and its quality, the actual values may deviate from these values Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m