



Glass Passivated Three Phase Rectifier Bridge


VRRM 800 to 1800V
ID 75 A

Applications

- Three phase rectifiers for power supplies
- Rectifiers for DC motor field supplies
- Battery charger rectifiers
- Input rectifiers for variable frequency drives

Features

- Three phase bridge rectifier
- Blocking voltage:800 to 1800V
- Heat transfer through aluminum oxide DBC ceramic isolated metal baseplate
- Glass passivated chip
- UL recognized applied for file no. E360040



Module Type

TYPE	VRRM	VRSM
MD75S08M2	800V	900V
MD75S12M2	1200V	1300V
MD75S16M2	1600V	1700V
MD75S18M2	1800V	1900V

Maximum Ratings

Symbol	Conditions	Values	Units
ID	Three phase, full wave Tc=110℃	75	A
IFSM	t=10mS Tvj =45℃	750	A
i ² t	t=10mS Tvj =45℃	2800	A ² s
Visol	a.c.50HZ;r.m.s.;1min	3000	V
Tvj		-40 to +150	℃
Tstg		-40 to +125	℃
Mt	To terminals(M5)	5±15%	Nm
Ms	To heatsink(M5)	5±15%	Nm
Weight	Module (Approximately)	130	g

Thermal Characteristics






Symbol	Conditions	Values	Units
Rth(j-c)	Per diode	1.1	℃/W
Rth(c-s)	Module (Approximately)	0.07	℃/W

Electrical Characteristics

Symbol	Conditions	Values			Units
		Min.	Typ.	Max.	
VFM	T=25℃ IF =150A	—	1.38	1.60	V
IRD	Tvj=25℃ VRD=VRRM Tvj=150℃ VRD=VRRM	—	—	0.3 5	mA mA




Performance Curves



Package Outline Information

CASE: M2



Dimensions in mm