

Bell suction cup (round)

SAX 50 ED-85 G3/8-IG

Part no.:10.01.19.00150

<https://www.schmalz.com/10.01.19.00150>



Homepage > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Sheet Metal >

Bell-Shaped Suction Cups SAX > SAX 50 ED-85 G3/8-IG

Bell suction cup (round) for best adaptation to strongly curved surfaces



Size: 50


Suction cup material: Elastodur

Material hardness: 85 °Sh

Vacuum connection: G3/8"-F

Nipple material: TPU-GF

Design Data



Attribute	Value
-----------	-------

dn	6.75 mm
----	---------

Dmax(S)	58.4 mm
---------	---------

Ds	51.5 mm
----	---------

G1	G3/8"-IG
----	----------

H	29.6 mm
---	---------

LG1	12 mm
-----	-------

SW1	22 mm
-----	-------

Z (Stroke)	8.4 mm
------------	--------

Technical Data

[Contact to Schmalz](#)

Schmalz Sp.z.o.o. | Kobaltowa 4, 62-002 Złotniki, Polen | +48 22 460 49 70 | schmalz@schmalz.pl

Page 1 of 2

Bell suction cup (round)

SAX 50 ED-85 G3/8-IG

Part no.:10.01.19.00150

<https://www.schmalz.com/10.01.19.00150>



Attribute	Value
Suction force (-600mbar)	109 N
Lateral force	74 N
Lateral force (oily surface)	110 N
Volume	15.2 cm ³
Curve radius (min) (convex)	25 mm
Size	50
Connection	G3/8"-F
Number of folds	0
Suction cup material	Elastodur
Material hardness [Shore A]	85 Shore A
Weight	26.2 g
Product family	SAX