


EL3062 | 2-channel analog input terminal 0...10 V, single-ended, 12 bit

The EL3062 analog input terminal processes signals in the range between 0 and 10 V. The voltage is digitised to a resolution of 12 bits and is transmitted, electrically isolated, to the higher-level automation device. The input channels of the EtherCAT Terminal have the reference ground as common ground potential. The signal state of the EtherCAT Terminal is indicated by light emitting diodes.

Technical data	EL3062 ES3062
Number of inputs	2 (single-ended)
Power supply	via the E-bus
Technology	single-ended
Signal voltage	0...10 V
Distributed clocks	–
Internal resistance	> 130 kΩ
Input filter limit frequency	1 kHz
Dielectric strength	max. 30 V
Conversion time	0.625 ms default setting, configurable, multiplex
Resolution	12 bit (16 bit presentation incl. sign)
Measuring error	< ±0.3 % (relative to full scale value)
Electrical isolation	500 V (E-bus/signal voltage)
Current consumption power contacts	–
Current consumption E-bus	typ. 130 mA
Bit width in the process image	inputs: 8 byte
Special features	activatable FIR/IIR filters, limit value monitoring
Weight	approx. 60 g
Operating/storage temperature	-25...+60 °C/-40...+85 °C
Relative humidity	95 %, no condensation
Vibration/shock resistance	conforms to EN 60068-2-6/EN 60068-2-27
EMC immunity/emission	conforms to EN 61000-6-2/EN 61000-6-4
Protect. class/installation pos.	IP 20/variable
Pluggable wiring	for all ESxxxx terminals
Approvals/markings	CE, UL, ATEX
Ex-Marking	II 3 G Ex nA IIC T4 Gc

Special terminals	
EL3062-0030	signal voltage 0...30 V