




EL2008 | 8-channel digital output terminal 24 V DC, 0.5 A

The EL2008 digital output terminal connects the binary control signals from the automation unit on to the actuators at the process level with electrical isolation. The EtherCAT Terminal indicates its signal state via an LED.

Technical data	EL2008 ES2008
Connection technology	1-wire
Number of outputs	8
Nominal voltage	24 V DC (-15 %/+20 %)
Load type	ohmic, inductive, lamp load
Distributed clocks	–
Max. output current	0.5 A (short-circuit proof) per channel
Short-circuit current	typ. < 2 A
Reverse voltage protection	yes
Breaking energy	< 150 mJ/channel
Switching times	typ. T _{ON} : 60 µs, typ. T _{OFF} : 300 µs
Current consumption E-bus	typ. 110 mA
Electrical isolation	500 V (E-bus/field potential)
Current consumption power contacts	typ. 15 mA + load
Bit width in the process image	8 outputs
Configuration	no address or configuration setting
Weight	approx. 55 g
Operating/storage temperature	-25...+60 °C/-40...+85 °C
Relative humidity	95 %, no condensation
Vibration/shock resistance	conforms to EN 60068-2-6/EN 60068-2-27
EMC immunity/emission	conforms to EN 61000-6-2/EN 61000-6-4
Protect. class/installation pos.	IP 20/see documentation
Pluggable wiring	for all ESxxxx terminals
Approvals/markings	CE, UL, ATEX, IECEx
Ex-Marking	II 3 G Ex nA IIC T4 Gc Ex nA IIC T4 Gc Ex tc IIIC T135 °C Dc