

REVISION RECORD			
REV	ECN	DESCRIPTION	DRFT

Technical characteristics:

Specifications

DIN EN 60 664-1

DIN EN 61 984

Inserts

01. Number of contacts :16+PE

02. Rated Current :16A

03. Rated Voltage :500V

04. Pollution degree :3

05. Rated impulse voltage :6kv_u06. Insulation resistance : $\geq 10^9 \Omega$

07. Material:Polycarbonate

08. Rated voltage acc.to UL/CSA:600V

09. Limiting temperatures : $-40^{\circ}\text{C}\sim+125^{\circ}\text{C}$

10. Flammability acc.to UL94:V0

11. Mechanical working life

(mating cycles) : ≥ 500

Contacts

01. Material:Copper alloy

02. Surface:hard-silver plated




03. Contact resistance : $\leq 1\text{m}\Omega$


04. Terminal :Crimp terminal

05. Wire gauge :0.14-4.0mm² (AWG 26-12)

06. Stripping length :7.5mm

07. Rohs Compliance

Note:Crimp contact pins should
order separately

PART NO.: /		NINGBO DEGSON ELECTRICAL CO., LTD	
APPD: HJS 2016.8.6		NAME: DE-016-MC	
CHKD: Ljm 2016.9.5		TITLE: CUSTOMER DRAWING	
DRFT: Mr. Yang 2016.08.08		DRAWING NO.: /	
		DO NOT SCALE DRAWING	
THIRD ANGLE PROJECTION		SCALE 1:1	