


THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	-,-
© COPYRIGHT - By -	ALL RIGHTS RESERVED.	




REVISIONS					
P	LTR	DESCRIPTION	DATE	OWN	APVD
	G1	REVISED PER ECO-11-004820	11MAR11	RK	HMR
	H	REVISED PER ECO-17-000037	10MAR2017	RS	MZ

NOTES:

1. WILL ACCEPT (19) MULTIMATE SOCKET CONTACTS.
2. CONTACT CAVITIES IDENTIFIED BY CHARACTERS ON FRONT AND REAR FACES OF CONNECTOR.
3. 3.81[.150] MAX INSULATION DIAMETER.
4. 2.54[.100] MAX INSULATION DIAMETER.




C
4 PLC




PANEL CUTOUT

211773-1, 211773-2 & 211773-6




211773-4



211773-5

③	OBSOLETE	4—40 THREADED INSERTS	YES	NORMAL	211773—6
③	OBSOLETE	—	NO	FREE HANGING	211773—5
③	OBSOLETE	—	NO	FREE HANGING	211773—4
④	—	ø3.81 [.150]	NO	NORMAL	211773—2
③	—	ø3.81 [.150]	NO	NORMAL	211773—1

C		PERIPHERAL SEAL		KEYING		PART NUMBER	
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. URICH 02JAN01 CHK M. CHACO 02JAN01 APVD M. CHACO 02JAN01		 TE Connectivity RECEPTACLE HOUSING, REVERSE SEX, SERIES I, SHELL SIZE 23, CPC			
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 3 PLC ± 0.13[.005] 4 PLC ± - ANGLES ± -					
MATERIAL NYLON, BLACK FINISH -		WEIGHT -		SIZE CAGE CODE DRAWING NO A1 00779 C-211773		RESTRICTED TO -	
CUSTOMER DRAWING				SCALE 1:1 SHEET 1 of 1 REV H			