


SKiiP 23NAB126V20



MiniSKiiP®2

3-phase bridge rectifier +
brake chopper + 3-phase
bridge inverter
SKiiP 23NAB126V20

Preliminary Data

Features


- Fast Trench IGBTs
- Robust and soft freewheeling diodes in CAL technology
- Highly reliable spring contacts for electrical connections
- UL recognised file no. E63532

Typical Applications*

- Inverter up to 16 kVA
- Typical motor power 7 kW

Remarks







- V_{CEsat} , V_F = chip level value









NAB

Absolute Maximum Ratings		$T_S = 25^{\circ}\text{C}$, unless otherwise specified	
Symbol	Conditions	Values	Units
IGBT - Inverter, Chopper			
V_{CES}	$T_s = 25\ (70)^{\circ}\text{C}$	1200	V
I_C		41 (31)	A
I_{CRM}		50	A
V_{GES}		± 20	V
T_j		-40...+150	$^{\circ}\text{C}$
Diode - Inverter, Chopper			
I_F	$T_s = 25\ (70)^{\circ}\text{C}$	27 (21)	A
I_{FRM}		50	A
T_j		-40...+150	$^{\circ}\text{C}$
Diode - Rectifier			
V_{RRM}	$T_s = 70^{\circ}\text{C}$	1600	V
I_F		46	A
I_{FSM}		370	A
i^2t		680	A^2s
T_j		-40...+150	$^{\circ}\text{C}$
Module			
I_{tRMS}	per power terminal (20 A / spring)	40	A
T_{stg}		-40...+125	$^{\circ}\text{C}$
V_{isol}	AC, 1 min.	2500	V

Characteristics		$T_S = 25^\circ\text{C}$, unless otherwise specified			
Symbol	Conditions	min.	typ.	max.	Units
IGBT - Inverter, Chopper					
V_{CEsat}	$I_{Cnom} = 25\text{ A}$, $T_j = 25\ (125)^\circ\text{C}$		1,7 (2)	2,1 (2,4)	V
$V_{GE(th)}$	$V_{GE} = V_{CE}$, $I_C = 1\text{ mA}$	5	5,8	6,5	V
$V_{CE(TO)}$	$T_j = 25\ (125)^\circ\text{C}$		1 (0,9)	1,2 (1,1)	V
r_T	$T_j = 25\ (125)^\circ\text{C}$		28 (44)	36 (52)	m Ω
C_{ies}	$V_{CE} = 25\text{ V}$, $V_{GE} = 0\text{ V}$, $f = 1\text{ MHz}$		1,8		nF
C_{oes}	$V_{CE} = 25\text{ V}$, $V_{GE} = 0\text{ V}$, $f = 1\text{ MHz}$		0,3		nF
C_{res}	$V_{CE} = 25\text{ V}$, $V_{GE} = 0\text{ V}$, $f = 1\text{ MHz}$		0,2		nF
$R_{th(j-s)}$	per IGBT		0,9		K/W
$t_{d(on)}$	under following conditions		75		ns
t_r	$V_{CC} = 600\text{ V}$, $V_{GE} = \pm 15\text{ V}$		30		ns
$t_{d(off)}$	$I_{Cnom} = 25\text{ A}$, $T_j = 125^\circ\text{C}$		460		ns
t_f	$R_{Gon} = R_{Goff} = 30\ \Omega$		90		ns
E_{on}	inductive load		2,7		mJ
E_{off}			2,9		mJ
Diode - Inverter, Chopper					
$V_F = V_{EC}$	$I_{Fnom} = 25\text{ A}$, $T_j = 25\ (125)^\circ\text{C}$		2,4 (2,2)	2,9 (2,7)	V
$V_{(TO)}$	$T_j = 25\ (125)^\circ\text{C}$		0,9 (0,6)	1,1 (0,8)	V
r_T	$T_j = 25\ (125)^\circ\text{C}$		60 (64)	72 (76)	m Ω
$R_{th(j-s)}$	per diode		1,5		K/W
I_{RRM}	under following conditions		30,2		A
Q_{rr}	$I_{Fnom} = 25\text{ A}$, $V_R = 600\text{ V}$		3,1		μC
E_{rr}	$V_{GE} = 0\text{ V}$, $T_j = 125^\circ\text{C}$		1,2		mJ
	$di_F/dt = 1200\text{ A}/\mu\text{s}$				
Diode - Rectifier					
V_F	$I_{Fnom} = 25\text{ A}$, $T_j = 25^\circ\text{C}$		1,1		V
$V_{(TO)}$	$T_j = 150^\circ\text{C}$		0,8		V
r_T	$T_j = 150^\circ\text{C}$		13		m Ω
$R_{th(j-s)}$	per diode		1,25		K/W
Temperature Sensor					
R_{ts}	3 %, $T_r = 25\ (100)^\circ\text{C}$		1000(1670)		Ω
Mechanical Data					
w			65		g
M_s	Mounting torque	2		2,5	Nm







This is an electrostatic discharge sensitive device (ESDS), international standard IEC 60747-1, Chapter IX.

* The specifications of our components may not be considered as an assurance of component characteristics. Components have to be tested for the respective application. Adjustments may be necessary. The use of SEMIKRON products in life support appliances and systems is subject to prior specification and written approval by SEMIKRON. We therefore strongly recommend prior consultation of our personal.