

Bell suction cup (round)

FSG 7 HT1-60 G1/8-AG

Part no.:10.01.06.01236

<https://www.schmalz.com/10.01.06.01236>



Homepage > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Bellows Suction Cups (Round) > Bellows

Suction Cups FSG (2.5 Folds) > FSG 7 HT1-60 G1/8-AG

Bellows suction cup (round) for very uneven workpieces



Size: 7

Suction cup material:

High temp material HT1

Material hardness: 60 °Sh


Material property: non-marking

Nipple material: Aluminium

Vacuum connection: G1/8"-M

Number of folds: 2.5

Design Data



Attribute

Value

d2 1.8 mm

dn 3.5 mm

Dmax(S) 9 mm

Ds 5.9 mm

G1 G1/8"-AG

H 20 mm

LG1 7.5 mm

SW1 14 mm

Z (Stroke) 3 mm

Technical Data

[Contact to Schmalz](#)

Schmalz Sp.z.o.o. | Kobaltowa 4, 62-002 Złotniki, Polen | +48 22 460 49 70 | schmalz@schmalz.pl

Page 1 of 3

Bell suction cup (round)

FSG 7 HT1-60 G1/8-AG

Part no.:10.01.06.01236


<https://www.schmalz.com/10.01.06.01236>



Attribute	Value
Suction cup material	High temp material HT1
Material hardness [Shore A]	60 Shore A
Size	7
Number of folds	2.5
Connection	G1/8-AG
Curve radius (min) (convex)	7.5 mm
Volume	0.043 cm ³
Suction force (-600mbar)	0.15 N
Pull-off force	0.9 N
Hose diameter (empf.) d	4 mm
Weight	4.3 g
Product family	FSG

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a smooth, dry workpiece surface - they do not include a safety factor Pull-off force: The pull-off force of the versions made of natural rubber is reduced by about 40% Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Spare Parts



SA-NIP N016 G1/8-AG DN350

Part no.10.01.06.05735

Suction cup connection nipple

Nipple: N 016

Thread G1: G1/8"-M

Overall length: 20 mm

Fitting length: 6 mm

Nominal size: 3,50 mm

Material: Aluminium

Bell suction cup (round)

FSG 7 HT1-60 G1/8-AG

Part no.:10.01.06.01236

<https://www.schmalz.com/10.01.06.01236>



FG 7 HT1-60 N016

Part no.10.01.06.01251

Bellows suction cup (round) for very uneven workpieces

Size: 7

Suction cup material:

High temp material HT1

Material hardness: 60 °Sh

Number of folds: 2.5

Material property: imprint-free