

Plug union, straight STV-GE G1/4-AG 4

Part no.:10.08.02.00203

<https://www.schmalz.com/10.08.02.00203>

Homepage > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connectors > Screw in Push Fittings > STV-GE G1/4-AG 4




Push-in Fitting, straight



Thread G1: G1/4"-M
External hose diameter: 4 mm
Material: Brass
Surface: nickel plated
Ambient temperature: -20 ... 80 °C

Design Data



Attribute	Value
-----------	-------

D	8.6 mm
---	--------

d	4 mm
---	------

G1	G1/4"-AG
----	----------

dn	4 mm
----	------

L	11.8 mm
---	---------

L1	19.6 mm
----	---------

L2	7.3 mm
----	--------

LG1	7.8 mm
-----	--------

SW1	17 mm
-----	-------

Technical Data

[Contact to Schmalz](#)

Schmalz Sp.z.o.o. | Kobaltowa 4, 62-002 Złotniki, Polen | +48 22 460 49 70 | schmalz@schmalz.pl

Page 1 of 3

Plug union, straight

STV-GE G1/4-AG 4


Part no.:10.08.02.00203

<https://www.schmalz.com/10.08.02.00203>



Attribute	Value
Hose type	Schlauch D = 4 d = 2
Hose type	4-2
Material	Messing
Pressure range (operating pressure)	-0,95 ... 15,00 bar
Operating temperature	-20 ... 80 °C
Weight	15 g

Accessories



VSL 4-2 PE

Part no.10.07.09.00013

Hose for vacuum and compressed-air systems

External diameter D: 4 mm

Internal diameter d: 2 mm

Length (max): 100 m

Material: PE

Installation radius (min): 20 mm

Pressure range (operating pressure):

-0.95 ... 10.00 bar

Ambient temperature: -30 ... 70 °C



VSL 4-2 PU

Part no.10.07.09.00001

Hose for vacuum and compressed-air systems

External diameter D: 4 mm

Internal diameter d: 2 mm

Length (max): 50 m

Material: PU

Installation radius (min): 20 mm

Pressure range (operating pressure):

-0.95 ... 10.00 bar

Ambient temperature: -40 ... 60 °C

Plug union, straight STV-GE G1/4-AG 4

Part no.:10.08.02.00203

<https://www.schmalz.com/10.08.02.00203>



VSL 4-2.7 PA

Part no.10.07.09.00063

Hose for vacuum and compressed-air systems

External diameter D: 4 mm

Internal diameter d: 2.7 mm

Length (max): 50 m

Material: PA

Installation radius (min): 30 mm

Pressure range (operating pressure):

-0.95 ... 20.00 bar

Ambient temperature: -40 ... 90 °C