





Notes:

- 1.Color:Natural;
- 2.RoHS Compliant;
- 3.Top Hole:Ø4.8±0.08mm,
Panel Thickness:1.6mm;
- 4.Bottom Hole:Ø4.8±0.08mm,
Panel Thickness:1.6mm.

Part No.	Part Name	Part No.	Part Name	A
41078	8G817V41078	41584	8G817V41584	3.0
41079	8G817V41079	41585	8G817V41585	4.0
41080	8G817V41080	41586	8G817V41586	6.0
41081	8G817V41081	41587	8G817V41587	8.0
41082	8G817V41082	41588	8G817V41588	10.0
41083	8G817V41083	41589	8G817V41589	12.0
41084	8G817V41084	41590	8G817V41590	14.0
41085	8G817V41085	41591	8G817V41591	16.0
41086	8G817V41086	41592	8G817V41592	18.0
Material: PA66 UL94 V2		Material: PA66 UL94 V0		

DREMEC Befestigungselemente GmbH						DATE	2020.03.03	DIMENSION	TOLERANCE
TITLE	DUAL LOCKING CIRCUIT BOARD SUPPORT					SCALE	FIT	L≤4	±0.10
PART NAME	8G817V41078	MOLD NO.	S0316/49	DRAW	PLK	UNIT	MM	4<L≤15	±0.20
PART NO.	SEE TABLE	MATERIAL	SEE TABLE	DESIGN	PLK	VERSION	A0	15<L≤50	±0.30
DWG NO.	E4112	COLOR	SEE NOTES	APPROVAL	FDL	VIEW		50<L≤100	±0.40