


Notes:

- 1.Color:Natural;
- 2.ROHS Compliant;
- 3.Top Hole: Ø4.75±0.08mm,
Panel Thickness: 0.79-1.98mm;
- 4.Bottom Hole: Ø4.75±0.08mm,
Panel Thickness: 0.79-1.98mm.

Part No.	Part Name	Part No.	Part Name	A
40829	8G818V40829	42012	8G818V42012	4.8
40830	8G818V40830	42013	8G818V42013	6.4
42681	8G818V40681	42682	8G818V42682	7.9
40831	8G818V40831	42014	8G818V42014	9.5
42462	8G818V42462	42463	8G818V42463	11.1
40832	8G818V40832	42015	8G818V42015	12.7
42458	8G818V42458	42459	8G818V42459	14.3
40833	8G818V40833	42016	8G818V42016	15.9
40834	8G818V40834	42017	8G818V42017	19.1
40835	8G818V40835	42018	8G818V42018	22.2
Material: PA66 UL94 V2		Material: PA66 UL94 V0		

DREMEC Befestigungselemente GmbH						DATE	2020-02-21	DIMENSION	TOLERANCE
TITLE	DUAL LOCKING CIRCUIT BOARD SUPPORT					SCALE	FIT	L≤4	±0.10
PART NAME	8G818V40829	MOLD NO.	S0396/7	DRAW	PLK	UNIT	MM	4<L≤15	±0.20
PART NO.	SEE TABLE	MATERIAL	SEE TABLE	DESIGN	PLK	VERSION	A0	15<L≤50	±0.30
DWG NO.	E4073	COLOR	SEE NOTES	APPROVAL	FDL	VIEW		50<L≤100	±0.40