

BiTLAN S/FTP cat.7A LSOH

1200 MHz

Halogen-free, data transmission cable, screened



internal
application



EN 60332-1



data transmission



halogen-free
EN 60754



low smoke emission
EN 61034

Technical data:

Temperature range:

Operating temperature: -30°C to +70°C

Min. installation temp: -10°C

Bending radius: 6xØ

Conductor diameter: 0,64±0,015mm

Insulated core diameter: 1,50±0,01mm

DC loop resistance at 20°C (max): 125Ω/km

Insulation resistance (min): 5GΩxkm

Resistance unbalance: ≤2%

Capacitance at 1 kHz: 45±5nF/km

Capacitance unbalance at 1kHz (max):

1600pF/km

Nominal voltage: 150V

Test voltage - 1min:

AC 50 Hz: 700V

DC: 1000V

Characteristic impedance: 100±5Ω

NVP value: 77%

Return loss (min):

f = 4÷10MHz: 20+5lg(f)

f = 10÷20MHz: 25

f = 20÷350MHz: 25-7lg(f/20)

f = 250÷600MHz: 17,3

f = 600÷1000MHz: 17,3-10lg(f/600)

Coupling attenuation within the range

of 30÷100 MHz (min.): 70dB

Transfer impedance at 10 MHz (max):

10mΩ/m

Construction:

Conductors: solid round copper conductors

Insulation: special polyolefin compound, foam-skin

Core identification: wh/bu-bu, wh/or-or, wh/gn-gn, wh/bn-bn

Core arrangement: cores twisted in pairs, screened pairs twisted together

Screen 1: aluminium backed polyester tape on every pair and tinned copper drain wire

Screen 2: tinned copper wire braid

Outer sheath: special LSOH compound

Outer sheath colour: orange RAL 2003

Marking: BITNER BiTLAN S/FTP 4x2x22AWG cat.7A 1200MHz LSOH

EN 50173-1 ISO/IEC 11801-1 IEC 61156-5 ID no. CE RoHS www.bitner.com.pl
meters


Application:

BiTLAN S/FTP cat.7A LSOH cables are applicable to computer networks with operating frequency band up to 1200MHz. Suitable for transmission of data, audio and video signals, with bitrate up to 10Gb/s. Additional individual and collective Al/Pet screens with CuSn drain wire acts as a protection against external electromagnetic interferences. Dedicated for fixed installations within indoor structured cabling systems as per EN 50173-1, ISO/IEC 11801, ANSI/TIA 568-C.2 standards, as well as within industrial networks exposed to external electromagnetic interferences.

Cables with flame retardant LSOH outer sheath ensuring low smoke emission acc. to EN 50268-2, IEC 61034-2 and limited emission of corrosive gases acc. to EN 60754-2, IEC 60754-2. should be installed in places with increased fire safety requirements.

Cables classified according to **EN 50575 (CPR)**.

Packaging:



Spool/Coil
500m



Spool/drum
1000m

Cat. no	Construction	Cu wire	O.D. [mm]	Cu [kg/km]	Cable weight [kg]	Bandwidth [MHz]
TI0089	S/FTP cat.7A LSOH	0,64	9,4	30	69	1200

Cable Factory BITNER reserves the right to modify the specifications without prior notice

BiTLAN S/FTP cat.7A LSOH

1200 MHz

Halogen-free, data transmission cable,
screened

Performance test charts and data:

Frequency MHz	1	4	10	16	20	31,25	62,5	100	155	200	300	600	750	900	1000	1200
Attenuation $\leq$ dB/100m	2,0	3,7	5,8	7,3	8,2	10,2	14,5	18,5	23,2	26,5	32,7	47,1	53,1	58,5	61,9	68,4
NEXT $\geq$ dB/100m	78,0	78,0	78,0	78,0	78,0	78,0	78,0	75,4	72,5	70,9	68,2	63,7	62,3	61,1	60,4	59,2
PS NEXT $\geq$ dB/100m	75,0	75,0	75,0	75,0	75,0	75,0	75,0	72,4	69,5	67,9	65,2	60,7	59,3	58,1	57,4	56,2
ELFEXT $\geq$ dB/100m	78,0	78,0	78,0	78,0	78,0	75,5	69,5	65,3	61,5	59,3	55,8	49,7	47,8	46,2	45,3	43,7
PS ELFEXT $\geq$ dB/100m	75,0	75,0	75,0	75,0	75,0	72,5	66,5	62,3	58,5	56,3	52,8	46,7	44,8	43,2	42,3	40,7
RL $\geq$ dB	20,0	23,0	25,0	25,0	25,0	23,7	21,6	20,1	18,8	18,0	17,3	17,3	16,3	15,5	15,1	14,3

Transmission parameters graphs - examples of measurement results

