





ISS.	AMEND	DATE
1 2	ISSUED USAGE NOTES	02/09/19 07/10/19




2 HOLES: Ø3.5MM
CSK 82° X Ø5.85
'X' VARIANT HAS PLAIN Ø2.5 HOLE



Materials:
Frame: PA66, UL94-V2
Insert: ABS - UL94 HB

USB-C Specification:
Maximum Rated Current - 3A
Maximum Power - 60W
Withstanding Voltage - 100V for 1 minute.
Contact Resistance - 40 Milli-ohms Max.
Insulation Resistance - 100 Mega-ohms Min.
Insertion Life - 5,000 Cycles.



WIRING DIAGRAM

FRONT REAR

A1 A12 B1 B12	—	A1 A12 B1 B12
A4 A9 B4 B9	—	A4 A9 B4 B9
A5	—	A5
B5	—	B5
A6 B6	—	A6 B6
A7 B7	—	A7 B7
A2	—	B11
A3	—	B10
B11	—	A2
B10	—	A3
B2	—	A11
B3	—	A10
A11	—	B2
A10	—	B3
A8	—	B8
B8	—	A8
SHELL	—	SHELL

RoHS
COMPLIANT

TOLERANCE

NO DEC. PLACE ± 0.50
1 DEC. PLACE ± 0.20
2 DEC. PLACE ± 0.10
HOLE Ø ± 0.10
ANGLES ± 1/2°
UNLESS
OTHERWISE STATED

DO NOT SCALE

VARIANTS	
PART NO.	DESCRIPTION
CP30201	HOLE Ø3.5MM CSK 82° X Ø5.85MM
CP30201X	PLAIN HOLE 2.5MM

FUNCTIONALITY IS AFFECTED BY CABLE QUALITY, LENGTH AND CABLE WIRING CONFIGURATION
NOT COMPATIBLE FOR POWER DELIVERY (PD) CHARGING

Cliff Electronic Components Ltd.

76 Holmethorpe Avenue, Holmethorpe Industrial Estate,
Redhill, Surrey, RH1 2PF, England, UK
Tel: 01737-771375 Fax: 01737-766012 Website: www.cliffuk.co.uk

DIMENSIONS IN MILLIMETERS UNLESS OTHERWISE STATED. WORK TO DIMENSIONS. REMOVE ALL BURRS. IF IN DOUBT ASK.

3rd ANGLE PROJECTION:

MATERIAL: SEE NOTES

FINISH: CLEAN

DRAWN: D P I

APPROVED: D P I

TITLE: FT USB-C (F-F) CSK

DRWG. No. CP30201

FORM: A4DRWGI

THE CONTENTS OF THIS DOCUMENT MUST NOT BE COPIED OR DISCLOSED
TO A 3rd PARTY WITHOUT WRITTEN PERMISSION OF CLIFF UK.