



Identification	Type	LCIS-WAA-0538-62-S
	Part-No.	750538.0000
Description	Input: 4–20 mA Output: 0–10 V / 0–20 mA / 4–20 mA Insulation: 2.5 kV, 3-way isolation	
Input		
Input signal	4–20 mA	
Galvanic isolation I/O	3-way isolation	
Step response (10–90%)	6 ms	
Zero /Span	Production comparison	
Input resistance	100 Ω	
Output		
Output signal	4–20 mA	
Output voltage limit	min 0 V max 10.8 V for all output ranges with nominal upper limit 10 V	
Output current limit	min. 0 mA for all output ranges with nominal lower limit 0 mA min. 3.6 mA or all output ranges 4 – 20 mA max. 21.6 mA for all output ranges with nominal upper limit 20 mA	
Max. load impedance at I-output	500 Ω	
Residual ripple	<20 mV _{eff}	

16.08.2019 – Subject to technical modification

Part-No. 750538.0000

USA: LUTZE INC.

13330 South Ridge Drive • Charlotte, NC 28273, USA

Tel. +1 (704) 504-0222 • Fax +1 (704) 504-0223

www.lutze.com • info@lutze.com

United Kingdom: LÜTZE Ltd.

Unit 3, Sandy Hill Park

Sandy Way, Amington • GB-Tamworth, Staffs B77 4DU

Tel. +44 (0)1827 31333-0 • Fax +44 (0)1827 31333-2

www.lutze.com • sales.gb@lutze.co.uk



SYSTEMATIC TECHNOLOGY

Technical data sheet · Interface Technology

Operating data

Accuracy	0.1 % FSR @ 23 °C
Linearity error	0.05 % FSR
Rise time (10 - 90%)	6 ms
Build-up time (Accuracy 1%)	17 ms
Temperature coefficient	<150 ppm / K FSR
Critical frequency	30 Hz @ 3 dB

General

Rated voltage U_N	AC/DC 24 V
Operation voltage range	AC 19.2–26.4 V / DC 18.0–31.2 V
Status indication	LED green
Input/output protection	Overvoltage, current input with PTC fuse, short circuit-proof output
Rise time (10 - 90%)	6 ms
Insulation voltage input / output	2.5 kV _{eff}
Housing material	PA 6.6 (UL 94 V-0, NFF I2, F2)
Color of the housing	RAL 7012 basalt grey
Mounting	DIN rail mountable TS35 (EN 60715)
Protection class	IP20
Installation position	any
Connection type	Screwed terminal single wire 0.25 mm ² –2.5 mm ² / AWG 20–14 fine stranded wire with ferrule 0.25 mm ² –1.5 mm ² / AWG 20–16
Operation temperature range	-25 °C ... +60 °C
Storage temperature range	-40 °C ... +80 °C
Dimensions (w × h × d)	6.2 × 93.0 × 73.0 mm
Weight	0.029 kg/piece
PU	1 piece
Approvals	cULus (E135145) DNV GL
Standards	EN 60947-5-1

Failure Rate Prediction (MTBF)

Standards	Electronic components – Reliability – Reference conditions for failure rates and stress models for conversion: EN/IEC 61709 Failure Rates of Components – Expected values: SN 29500
Failure rate at +45 °C	504 fit
Failure rate at +45 °C	1983891 h

16.08.2019 – Subject to technical modification

Part-No. 750538.0000

USA: LUTZE INC.

13330 South Ridge Drive • Charlotte, NC 28273, USA

Tel. +1 (704) 504-0222 • Fax +1 (704) 504-0223

www.lutze.com • info@lutze.com

United Kingdom: LÜTZE Ltd.

Unit 3, Sandy Hill Park

Sandy Way, Amington • GB-Tamworth, Staffs B77 4DU

Tel. +44 (0)1827 31333-0 • Fax +44 (0)1827 31333-2

www.lutze.com • sales.gb@lutze.co.uk



SYSTEMATIC TECHNOLOGY

Technical data sheet • Interface Technology

Comments

1 fit equals one failure per 10^9 component hours


The indicated temperature is the mean component ambient temperature.

The results are valid under following conditions:


Automotive environment or industrial areas without extreme dust levels and harmful substances

Continuous operation 8760 h per year

Dimensions



PIN assignment



16.08.2019 – Subject to technical modification

Part-No. 750538.0000

USA: LUTZE INC.

13330 South Ridge Drive • Charlotte, NC 28273, USA

Tel. +1 (704) 504-0222 • Fax +1 (704) 504-0223

www.lutze.com • info@lutze.com

United Kingdom: LÜTZE Ltd.

Unit 3, Sandy Hill Park

Sandy Way, Amington • GB-Tamworth, Staffs B77 4DU

Tel. +44 (0)1827 31333-0 • Fax +44 (0)1827 31333-2

www.lutze.com • sales.gb@lutze.co.uk



SYSTEMATIC TECHNOLOGY