

HSK-Ex e CABLE GLANDS

HSK-K-Ex-Active

Metr.



Material	fibreglass reinforced polyamide
Seal	Buna-N
O-Ring	Buna-N
Protection	IP 68 – 10 bar within the specified clamping range
Operating Temperature	-20 °C – 85 °C (-4 °F – 185 °F)
Colors	black (RAL 9005) / blue-black (RAL 5012)

// FKM and VMQ O-Ring upon request




II 2G Ex eb IIC Gb
II TD Ex ta IIIC Da



Class I Div 2 Groups A, B, C, D
Class II Div 1 Groups E, F, G

For the [international certificates](http://www.hummel.com) go to www.hummel.com.



AG	Ø mm	mm	H mm	GL mm	Number black	Number blue-black	GL mm	Number black elongated	Number blue-black elongated
M 12 x 1,5	3–6,5	15	21	8	1.292.1201.50	1.292.1202.50	15	1.292.1201.30	1.292.1202.30
M 12 x 1,5	2–5	15	21	8	1.292.1201.51	1.292.1202.51	15	1.292.1201.31	1.292.1202.31
M 16 x 1,5	4–8	19	22	8	1.292.1601.50	1.292.1602.50	15	1.292.1601.30	1.292.1602.30
M 16 x 1,5	3–6	19	22	8	1.292.1601.51	1.292.1602.51	15	1.292.1601.31	1.292.1602.31
M 16 x 1,5	5–10	22	25	8	1.292.1611.50	1.292.1612.50	15	1.292.1611.30	1.292.1612.30
M 16 x 1,5	3–7	22	25	8	1.292.1611.51	1.292.1612.51	15	1.292.1611.31	1.292.1612.31
M 20 x 1,5	6–12	24	27	9	1.292.2001.50	1.292.2002.50	15	1.292.2001.30	1.292.2002.30
M 20 x 1,5	5–9	24	27	9	1.292.2001.51	1.292.2002.51	15	1.292.2001.31	1.292.2002.31
M 20 x 1,5	10–14	27	28	9	1.292.2016.50	1.292.2017.50	15	1.292.2016.30	1.292.2017.30
M 20 x 1,5	7–12	27	28	9	1.292.2016.51	1.292.2017.51	15	1.292.2016.31	1.292.2017.31
M 25 x 1,5	13–18	33	31	11	1.292.2501.50	1.292.2502.50	15	1.292.2501.30	1.292.2502.30
M 25 x 1,5	9–16	33	31	11	1.292.2501.51	1.292.2502.51	15	1.292.2501.31	1.292.2502.31
M 32 x 1,5	18–25	42	39	11	1.292.3201.50	1.292.3202.50	15	1.292.3201.30	1.292.3202.30
M 32 x 1,5	13–20	42	39	11	1.292.3201.51	1.292.3202.51	15	1.292.3201.31	1.292.3202.31
M 40 x 1,5	22–32	53	48	13	1.292.4001.50	1.292.4002.50	18	1.292.4001.30	1.292.4002.30
M 40 x 1,5	20–26	53	48	13	1.292.4001.51	1.292.4002.51	18	1.292.4001.31	1.292.4002.31
M 50 x 1,5	32–38	60	49	13	1.292.5001.50	1.292.5002.50	18	1.292.5001.30	1.292.5002.30
M 50 x 1,5	25–31	60	49	13	1.292.5001.51	1.292.5002.51	18	1.292.5001.31	1.292.5002.31
M 63 x 1,5	37–44	65/68	49	14	1.292.6301.50	1.292.6302.50	18	1.292.6301.30	1.292.6302.30
M 63 x 1,5	29–35	65/68	49	14	1.292.6301.51	1.292.6302.51	18	1.292.6301.31	1.292.6302.31
NPT 3/8"	4–8	19 / 22	22	15				1.292.3801.70	1.292.3802.70
NPT 3/8"	3–6	19 / 22	22	15				1.292.3801.71	1.292.3802.71
NPT 1/2"	6–12	24	27	13				1.292.1201.70	1.292.1202.70
NPT 1/2"	5–9	24	27	13				1.292.1201.71	1.292.1202.71
NPT 1/2" (16)	10–14	27	28	13				1.292.1216.70	1.292.1217.70
NPT 1/2" (16)	7–12	27	28	13				1.292.1216.71	1.292.1217.71
NPT 3/4"	13–18	33	31	14				1.292.3401.70	1.292.3402.70
NPT 3/4"	9–16	33	31	14				1.292.3401.71	1.292.3402.71
NPT 1"	18–25	42	39	19				1.292.1001.70	1.292.1002.70
NPT 1"	13–20	42	39	19				1.292.1001.71	1.292.1002.71
NPT 1 1/4"	18–25	42/46	39	16				1.292.5401.70	1.292.5402.70
NPT 1 1/4"	13–20	42/46	39	16				1.292.5401.71	1.292.5402.71
NPT 1 1/2"	22–32	53	48	20				1.292.6401.70	1.292.6402.70
NPT 1 1/2"	20–26	53	48	20				1.292.6401.71	1.292.6402.71