

Guide bushings

Drill bushings, with collar

SPECIFICATION

Type

- Type **A**: bore one-sided

Steel

hardened (HRC 62 ±2)

Fit sizes d₁, d₂ ground

INFORMATION

The dimensions listed in this standard sheet are merely a selection of the (currently withdrawn) DIN standards.

For applications involving positioning, we recommend the combination with the GN 771.1 guide pins (see page 1011).


For mounting bushings with tolerance n6, a hole with tolerance H7 corresponding to the external diameter is usually provided.

ON REQUEST

- other bores d₁

TECHNICAL INFORMATION

- ISO-Fundamental Tolerances (see page A21)



DIN 172

Description	d1 F7	l1	d2 n6	d3	l2	
DIN 172-B2-6-A	B 2	6	5	8	2	1
DIN 172-B2-9-A	B 2	9	5	8	2	1
DIN 172-B2,1-6-A	B 2.1	6	5	8	2	1
DIN 172-B2,1-9-A	B 2.1	9	5	8	2	2
DIN 172-B2,5-6-A	B 2.5 (M 3)	6	5	8	2	1
DIN 172-B2,5-9-A	B 2.5 (M 3)	9	5	8	2	1
DIN 172-B3-8-A	B 3	8	6	9	2.5	2
DIN 172-B3-12-A	B 3	12	6	9	2.5	3
DIN 172-B3-16-A	B 3	16	6	9	2.5	3
DIN 172-B3,1-8-A	B 3.1	8	6	9	2.5	2
DIN 172-B3,1-12-A	B 3.1	12	6	9	2.5	3
DIN 172-B3,1-16-A	B 3.1	16	6	9	2.5	3
DIN 172-B3,3-8-A	B 3.3 (M 4)	8	6	9	2.5	2
DIN 172-B3,3-12-A	B 3.3 (M 4)	12	6	9	2.5	2
DIN 172-B3,3-16-A	B 3.3 (M 4)	16	6	9	2.5	4
DIN 172-B3,5-8-A	B 3.5	8	7	10	2.5	2
DIN 172-B3,5-12-A	B 3.5	12	7	10	2.5	3
DIN 172-B3,5-16-A	B 3.5	16	7	10	2.5	4
DIN 172-B3,8-8-A	B 3.8	8	7	10	2.5	4
DIN 172-B3,8-12-A	B 3.8	12	7	10	2.5	4
DIN 172-B3,8-16-A	B 3.8	16	7	10	2.5	5
DIN 172-B4-8-A	B 4	8	7	10	2.5	2
DIN 172-B4-12-A	B 4	12	7	10	2.5	3
DIN 172-B4-16-A	B 4	16	7	10	2.5	4
DIN 172-B4,1-8-A	B 4.1	8	8	11	2.5	3
DIN 172-B4,1-12-A	B 4.1	12	8	11	2.5	4
DIN 172-B4,1-16-A	B 4.1	16	8	11	2.5	6
DIN 172-B4,2-8-A	B 4.2 (M 5)	8	8	11	2.5	3
DIN 172-B4,2-12-A	B 4.2 (M 5)	12	8	11	2.5	4
DIN 172-B4,2-16-A	B 4.2 (M 5)	16	8	11	2.5	4

DIN 172

Description	d1 F7	l1	d2 n6	d3	l2	
DIN 172-B4,5-8-A	B 4.5	8	8	11	2.5	3
DIN 172-B4,5-12-A	B 4.5	12	8	11	2.5	4
DIN 172-B4,5-16-A	B 4.5	16	8	11	2.5	4
DIN 172-B4,8-8-A	B 4.8	8	8	11	2.5	3
DIN 172-B4,8-12-A	B 4.8	12	8	11	2.5	4
DIN 172-B4,8-16-A	B 4.8	16	8	11	2.5	5
DIN 172-B5-8-A	B 5 (M 6)	8	8	11	2.5	2
DIN 172-B5-12-A	B 5 (M 6)	12	8	11	2.5	3
DIN 172-B5-16-A	B 5 (M 6)	16	8	11	2.5	4
DIN 172-B5,1-10-A	B 5.1	10	10	13	3	6
DIN 172-B5,1-16-A	B 5.1	16	10	13	3	8
DIN 172-B5,1-20-A	B 5.1	20	10	13	3	10
DIN 172-B5,5-10-A	B 5.5	10	10	13	3	5
DIN 172-B5,5-16-A	B 5.5	16	10	13	3	8
DIN 172-B5,5-20-A	B 5.5	20	10	13	3	10
DIN 172-B5,8-10-A	B 5.8	10	10	13	3	5
DIN 172-B5,8-16-A	B 5.8	16	10	13	3	8
DIN 172-B5,8-20-A	B 5.8	20	10	13	3	10
DIN 172-B6-10-A	B 6	10	10	13	3	5
DIN 172-B6-16-A	B 6	16	10	13	3	7
DIN 172-B6-20-A	B 6	20	10	13	3	9
DIN 172-B6,1-10-A	B 6.1	10	12	15	3	5
DIN 172-B6,1-16-A	B 6.1	16	12	15	3	12
DIN 172-B6,1-20-A	B 6.1	20	12	15	3	15
DIN 172-B6,5-10-A	B 6.5	10	12	15	3	7
DIN 172-B6,5-16-A	B 6.5	16	12	15	3	11
DIN 172-B6,5-20-A	B 6.5	20	12	15	3	14
DIN 172-B6,8-10-A	B 6.8 (M 8)	10	12	15	3	7
DIN 172-B6,8-16-A	B 6.8 (M 8)	16	12	15	3	11
DIN 172-B6,8-20-A	B 6.8 (M 8)	20	12	15	3	13

DIN 172

Description	d1 F7	l1	d2 n6	d3	l2	
DIN 172-B7-10-A	B 7	10	12	15	3	7
DIN 172-B7-16-A	B 7	16	12	15	3	11
DIN 172-B7-20-A	B 7	20	12	15	3	12
DIN 172-B7,5-10-A	B 7.5	10	12	15	3	7
DIN 172-B7,5-16-A	B 7.5	16	12	15	3	11
DIN 172-B7,5-20-A	B 7.5	20	12	15	3	13
DIN 172-B7,8-10-A	B 7.8	10	12	15	3	6
DIN 172-B7,8-16-A	B 7.8	16	12	15	3	9
DIN 172-B7,8-20-A	B 7.8	20	12	15	3	12
DIN 172-B8-10-A	B 8	10	12	15	3	6
DIN 172-B8-16-A	B 8	16	12	15	3	9
DIN 172-B8-20-A	B 8	20	12	15	3	13
DIN 172-B8,1-12-A	B 8.1	12	15	18	3	13
DIN 172-B8,1-20-A	B 8.1	20	15	18	3	21
DIN 172-B8,1-25-A	B 8.1	25	15	18	3	26
DIN 172-B8,5-12-A	B 8.5 (M 10)	12	15	18	3	12
DIN 172-B8,5-20-A	B 8.5 (M 10)	20	15	18	3	20
DIN 172-B8,5-25-A	B 8.5 (M 10)	25	15	18	3	24
DIN 172-B9-12-A	B 9	12	15	18	3	12
DIN 172-B9-20-A	B 9	20	15	18	3	19
DIN 172-B9-25-A	B 9	25	15	18	3	24
DIN 172-B9,5-12-A	B 9.5	12	15	18	3	11
DIN 172-B9,5-20-A	B 9.5	20	15	18	3	18
DIN 172-B9,5-25-A	B 9.5	25	15	18	3	23
DIN 172-B9,8-12-A	B 9.8	12	15	18	3	11
DIN 172-B9,8-20-A	B 9.8	20	15	18	3	17
DIN 172-B9,8-25-A	B 9.8	25	15	18	3	22
DIN 172-B10-12-A	B 10	12	15	18	3	10
DIN 172-B10-20-A	B 10	20	15	18	3	17
DIN 172-B10-25-A	B 10	25	15	18	3	21
DIN 172-B10,1-12-A	B 10.1	12	18	22	4	20
DIN 172-B10,1-20-A	B 10.1	20	18	22	4	30
DIN 172-B10,1-25-A	B 10.1	25	18	22	4	35
DIN 172-B10,2-12-A	B 10.2 (M 12)	12	18	22	4	20
DIN 172-B10,2-20-A	B 10.2 (M 12)	20	18	22	4	30
DIN 172-B10,2-25-A	B 10.2 (M 12)	25	18	22	4	37
DIN 172-B10,5-12-A	B 10.5	12	18	22	4	19
DIN 172-B10,5-20-A	B 10.5	20	18	22	4	29
DIN 172-B10,5-25-A	B 10.5	25	18	22	4	36
DIN 172-B11-12-A	B 11	12	18	22	4	18
DIN 172-B11-20-A	B 11	20	18	22	4	28
DIN 172-B11-25-A	B 11	25	18	22	4	35
DIN 172-B11,5-12-A	B 11.5	12	18	22	4	17
DIN 172-B11,5-20-A	B 11.5	20	18	22	4	28
DIN 172-B11,5-25-A	B 11.5	25	18	22	4	33
DIN 172-B11,8-12-A	B 11.8	12	18	22	4	17
DIN 172-B11,8-20-A	B 11.8	20	18	22	4	26
DIN 172-B11,8-25-A	B 11.8	25	18	22	4	32
DIN 172-B12-12-A	B 12	12	18	22	4	16
DIN 172-B12-20-A	B 12	20	18	22	4	25
DIN 172-B12-25-A	B 12	25	18	22	4	31
DIN 172-B12,1-16-A	B 12.1	16	22	26	4	37
DIN 172-B12,1-28-A	B 12.1	28	22	26	4	62
DIN 172-B12,1-36-A	B 12.1	36	22	26	4	97
DIN 172-B12,5-16-A	B 12.5	16	22	26	4	36
DIN 172-B12,5-28-A	B 12.5	28	22	26	4	60
DIN 172-B12,5-36-A	B 12.5	36	22	26	4	78
DIN 172-B13-16-A	B 13 (M 14)	16	22	26	4	35
DIN 172-B13-28-A	B 13 (M 14)	28	22	26	4	58

DIN 172

Description	d1 F7	l1	d2 n6	d3	l2	
DIN 172-B13-36-A	B 13 (M 14)	36	22	26	4	74
DIN 172-B13,5-16-A	B 13.5	16	22	26	4	33
DIN 172-B13,5-28-A	B 13.5	28	22	26	4	55
DIN 172-B13,5-36-A	B 13.5	36	22	26	4	71
DIN 172-B14-16-A	B 14 (M 16)	16	22	26	4	32
DIN 172-B14-28-A	B 14 (M 16)	28	22	26	4	53
DIN 172-B14-36-A	B 14 (M 16)	36	22	26	4	68
DIN 172-B14,1-16-A	B 14.1	16	22	26	4	32
DIN 172-B14,1-28-A	B 14.1	28	22	26	4	53
DIN 172-B14,1-36-A	B 14.1	36	22	26	4	68
DIN 172-B14,5-16-A	B 14.5	16	22	26	4	31
DIN 172-B14,5-28-A	B 14.5	28	22	26	4	51
DIN 172-B14,5-36-A	B 14.5	36	22	26	4	65
DIN 172-B15-16-A	B 15	16	22	26	4	29
DIN 172-B15-28-A	B 15	28	22	26	4	48
DIN 172-B15-36-A	B 15	36	22	26	4	61
DIN 172-B15,5-16-A	B 15.5	16	26	30	4	47
DIN 172-B15,5-28-A	B 15.5	28	26	30	4	79
DIN 172-B15,5-36-A	B 15.5	36	26	30	4	80
DIN 172-B16-16-A	B 16	16	26	30	4	46
DIN 172-B16-28-A	B 16	28	26	30	4	76
DIN 172-B16-36-A	B 16	36	26	30	4	98
DIN 172-B16,1-16-A	B 16.1	16	26	30	4	45
DIN 172-B16,1-28-A	B 16.1	28	26	30	4	75
DIN 172-B16,1-36-A	B 16.1	36	26	30	4	97
DIN 172-B16,5-16-A	B 16.5	16	26	30	4	44
DIN 172-B16,5-28-A	B 16.5	28	26	30	4	74
DIN 172-B16,5-36-A	B 16.5	36	26	30	4	95
DIN 172-B17-16-A	B 17	16	26	30	4	42
DIN 172-B17-28-A	B 17	28	26	30	4	71
DIN 172-B17-36-A	B 17	36	26	30	4	91
DIN 172-B18-16-A	B 18	16	26	30	4	39
DIN 172-B18-28-A	B 18	28	26	30	4	64
DIN 172-B18-36-A	B 18	36	26	30	4	83
DIN 172-B19-20-A	B 19	20	30	34	5	80
DIN 172-B19-36-A	B 19	36	30	34	5	124
DIN 172-B19-45-A	B 19	45	30	34	5	155
DIN 172-B20-20-A	B 20	20	30	34	5	100
DIN 172-B20-36-A	B 20	36	30	34	5	116
DIN 172-B20-45-A	B 20	45	30	34	5	145
DIN 172-B22-20-A	B 22	20	30	34	5	100
DIN 172-B22-36-A	B 22	36	30	34	5	110
DIN 172-B22-45-A	B 22	45	30	34	5	121
DIN 172-B24-20-A	B 24	20	35	39	5	133
DIN 172-B24-36-A	B 24	36	35	39	5	150
DIN 172-B24-45-A	B 24	45	35	39	5	186
DIN 172-B25-20-A	B 25	20	35	39	5	100
DIN 172-B25-36-A	B 25	36	35	39	5	138
DIN 172-B25-45-A	B 25	45	35	39	5	173
DIN 172-B26-20-A	B 26	20	35	39	5	100
DIN 172-B26-36-A	B 26	36	35	39	5	127
DIN 172-B26-45-A	B 26	45	35	39	5	159
DIN 172-B28-25-A	B 28	25	42	46	5	157
DIN 172-B28-45-A	B 28	45	42	46	5	277
DIN 172-B28-56-A	B 28	56	42	46	5	343
DIN 172-B30-25-A	B 30	25	42	46	5	139
DIN 172-B30-45-A	B 30	45	42	46	5	245
DIN 172-B30-56-A	B 28	56	42	46	5	303

