

Slide switches

Slide switches, THT, vertical



Highlights

- Miniature slide switches with 3 pin connection
- Can be used as ON/OFF-switches or CHANGE-OVER-switches
- End-stackable in 2.54 mm pitch
- Solder and flux sealed base
- Gold plated roller contacts ensure safe switching even at low currents
- Robust and reliable switches despite of miniature size
- Switching position A visible on the top
- High-end alternative to jumpers
- Can also be used as address switch for applications requiring a limited quantity of addresses

Mechanical Data

Fixation mode	THT
Pitch	2.54 mm
Switching mode	Contact wiping on make and break
Switching positions	2
Mechanical lifetime	5.000 operations
Operating force	8.0 N
Operating travel	1.5 mm
Perm. ambient temperature	-40 °C ... +85 °C
Perm. storage temperature	-40 °C ... +85 °C
Humidity	21 days at 95 %RH (IEC 60068-2-3)
Wave soldering	Single Wave

Electrical Data

Contact rating, switching	12.0 VDC / 0.5 A - 24.0 VDC / 0.2 A
Contact rating, non switching	10.0 mV / 0.01 A
Contact resistance initial	50.0 mOhm
Contact resistance after life test	100.0 mOhm
Insulation resistance	1.000 MOhm min. 100.0 VDC
Test voltage	500.0 VDC min. / 60.0 s
Capacitance	< 1.5 pF



PTR HARTMANN

A Phoenix Mecano Company


Technical data

// **SR254 T**

Slide switches


Slide switches, THT, vertical

Technical Drawing



Configuration

Packing



Tube