


T500, Tantalum, MnO₂ Tantalum, High Temperature, 15 uF, 10%, 25 VDC, SMD, MnO₂, Molded, High Temperature, 200C, N/A, 1 Ohms, 7343, Height Max = 3.1mm



Dimensions

Footprint	7343
L	7.3mm +/-0.3mm
W	4.3mm +/-0.3mm
H	2.8mm +/-0.3mm
T	0.13mm REF
S	1.3mm +/-0.3mm
F	2.4mm +/-0.1mm
A	3.8mm MIN
B	0.5mm +/-0.15mm
E	3.5mm REF
G	3.5mm REF
P	0.9mm REF
R	1mm REF
X	0.1mm +/-0.1mm

Packaging Specifications

Packaging:	T&R, 178mm
Packaging Quantity:	500

General Information

Series:	T500
Dielectric:	MnO ₂ Tantalum
Style:	SMD Chip
Description:	SMD, MnO ₂ , Molded, High Temperature, 200C
Features:	200C
RoHS:	Yes
Termination:	Gold
AEC-Q200:	No
Shelf Life:	156 Weeks
MSL:	1

Specifications

Capacitance:	15 uF
Capacitance Tolerance:	10%
Voltage DC:	25 VDC (85C), 20 VDC (125C), 10 VDC (200C)
Temperature Range:	-55/+200°C
Rated Temperature:	85°C
Humidity:	85C, 85% RH, 0 V, 1000 Hours
Dissipation Factor:	6% 120Hz 20C
Failure Rate:	N/A
Resistance:	1000 mOhms (100kHz 20C)
Ripple Current:	387 mA (rms, 100kHz 25C), 155 mA (rms, 100kHz 125C), 39 mA (rms, 100kHz 200C)
Leakage Current:	3.8 uA (5min 20°C)