




WN 1451



380 HV



BN 20095

Pan head PT® screws

with pressed-on disc and Torx®

Steel heat-treated 380 HV

zinc plated blue



ISO 4042

Quenched and tempered fasteners ≥ 360 HV and tempered case-hardened fasteners with electroplated coatings: Susceptible to hydrogen embrittlement! Further notice to residual risks can be found in the introduction section.



A technical brochure is available on request

Article#	ø nominal	d ₁	d ₂	k	s		A~	t min.	t max.	L
3205500	K30	3	6	2,1	0,6	T10	2,8	1	1,3	5
3205501										6
3351596										7
3205502										8
3205503										10
3205504										12
3205505										14
3205507										16
3205508	K35	3,5	7	2,4	0,7	T10	2,8	1,1	1,4	8
3205509										10
3205510										12
3205511										14
3205512										16
3205513										18
3205514										20
3351597	K40	4	8	2,6	0,8	T20	3,95	1,25	1,7	8
3205515										10
3205516										12
3205517										14
3205518										16
3205519										18
3205520										20

Article#	ø nominal	d ₁	d ₂	k	s		A~	t min.	t max.	L
3205521	K40	4	8	2,6	0,8	T20	3,95	1,25	1,7	25
3205522	K50	5	10	3,3	1	T20	3,95	1,4	1,8	10
3205523										12
3205524										16
3205525										20
3205526										25
3205528										30
3351598										35