

**BN 1014****Slotted pan head thread cutting screws**

with tapping screw thread type 1

Steel case-hardened 450 HV

zinc plated blue



ISO 4042

Quenched and tempered fasteners ≥ 360 HV and tempered case-hardened fasteners with electroplated coatings: Susceptible to hydrogen embrittlement!
Further notice to residual risks can be found in the introduction section.

[3D Cadenas](#)

hole-Ø: approximate data; the final hole diameters should be determined by performance tests.

Article#	d ₁	d ₂ max.	k max.	n	t min.	Ø - Ø	L
1381016	ST 2,2	4,2	1,35	0,6	0,55	1,8	6,5
1381024							9,5
1381032							13
1381059	ST 2,9	5,6	1,75	0,8	0,75	2,5	6,5
1381075							13
1398962							22
1381105							25
1381113	ST 3,5	6,9	2,1	1	0,95	3	6,5
1381121							9,5
1381156							16
1381164							19
1381180	ST 3,9	7,5	2,25	1	1,05	3,5	6,5
1381199							9,5
1381245	ST 4,2	8,2	2,45	1,2	1,15	3,8	13
1399012							22
1381261							25
1381296	ST 4,8	9,5	2,8	1,2	1,35	4,3	13
1381334	ST 5,5	10,8	3,2	1,6	1,55	5	13