




Notes:

- 1.Color:Natural;
- 2.RoHS Compliant;
- 3.Top Hole:Ø4.0±0.08mm,
Panel Thickness:1.57mm;
Bottom Hole:Ø4.75±0.08mm,
Panel Thickness:0.79-1.98mm;

Part No.	Part Name	A	Material
42516	8GG01V42516	4.8	PA66 UL94 V2
42494	8GG01V42494	6.4	
42517	8GG01V42517	9.5	
42518	8GG01V42518	12.7	
42519	8GG01V42519	15.9	
40975	8GG01V40975	19.1	
42520	8GG01V42520	22.2	
42521	8GG01V42521	4.8	PA66 UL94 V0
42522	8GG01V42522	6.4	
42523	8GG01V42523	9.5	
42524	8GG01V42524	12.7	
42525	8GG01V42525	15.9	
42526	8GG01V42526	19.1	
42527	8GG01V42527	22.2	

DREMEC Befestigungselemente GmbH

DATE

2020.02.27

DIMENSION

TOLERANCE

TITLE

LOCKING CIRCUIT BOARD SUPPORT

SCALE

FIT

L≤4

±0.10

PART NAME

8GG01V42516

MOLD NO.

S0643

DRAW

PLK

UNIT

MM

4<L≤15

±0.20

PART NO.

SEE TABLE

MATERIAL

SEE TABLE

DESIGN

PLK

VERSION

A0

15<L≤50

±0.30

DWG NO.

E4192


COLOR

SEE NOTES

APPROVAL

FDL

VIEW



50<L≤100

±0.40