


Notes:

- 1.Color:Natural;
- 2.RoHS Compliant;
- 3.Top Hole: $\varnothing 4.0 \pm 0.08 \text{ mm}$,
Panel Thickness: 0.79-1.98mm;
- 4.Bottom Hole: $\varnothing 4.0 \pm 0.08 \text{ mm}$,
Panel Thickness: 0.79-1.98mm.

Part No.	Part Name	Part No.	Part Name	A
40815	8G818V40815	40816	8G818V40816	4.8
40817	8G818V40817	40818	8G818V40818	6.4
42611	8G818V42611	42662	8G818V42662	7.9
40819	8G818V40819	40820	8G818V40820	9.5
42349	8G818V42349	42350	8G818V42350	11.1
40821	8G818V40821	40822	8G818V40822	12.7
42456	8G818V42456	42457	8G818V42457	14.3
40823	8G818V40823	40824	8G818V40824	15.9
40825	8G818V40825	40826	8G818V40826	19.1
40827	8G818V40827	40828	8G818V40828	22.2
Material: PA66 UL94 V2		Material: PA66 UL94 V0		

DREMEC Befestigungselemente GmbH						DATE	2020.03.02	DIMENSION	TOLERANCE
TITLE	DUAL LOCKING CIRCUIT BOARD SUPPORT					SCALE	FIT	$L \leq 4$	± 0.10
PART NAME	8G818V40815	MOLD NO.	S0396/7	DRAW	PLK	UNIT	MM	$4 < L \leq 15$	± 0.20
PART NO.	SEE TABLE	MATERIAL	SEE TABLE	DESIGN	PLK	VERSION	A0	$15 < L \leq 50$	± 0.30
DWG NO.	E4072	COLOR	SEE NOTES	APPROVAL	FDL	VIEW		$50 < L \leq 100$	± 0.40