





Part No.	Part Name	Part No.	Part Name	A
41190	8G808V41190	41765	8G807V41765	1.6
41191	8G808V41191	41766	8G807V41766	3.2
41192	8G808V41192	41767	8G807V41767	4.8
41193	8G808V41193	41768	8G807V41768	6.4
41194	8G808V41194	41769	8G807V41769	7.9
41195	8G808V41195	41770	8G807V41770	9.5
Material: PA66 UL94 V2 Color: Natural		Material: PA66 UL94 V0 Color: Natural		

Notes:

- 1.RoHS Compliant;
- 2.Top Hole: $\varnothing 2.5\pm 0.05\text{mm}$,
Panel Thickness: 1.6mm;
- 3.Bottom Hole: $\varnothing 2.0\pm 0.05\text{mm}$,
Panel Thickness: 1.0mm.

DREMEC Befestigungselemente GmbH						DATE	2020.03.05	DIMENSION	TOLERANCE
TITLE	DUAL LOCKING CIRCUIT BOARD SUPPORT					SCALE	FIT	L ≤ 4	±0.10
PART NAME	8G808V41500	MOLD NO.	S0301/2	DRAW	PLK	UNIT	MM	4 < L ≤ 15	±0.20
PART NO.	SEE TABLE	MATERIAL	SEE TABLE	DESIGN	PLK	VERSION	A0	15 < L ≤ 50	±0.30
DWG NO.	E4128	COLOR	SEE TABLE	APPROVAL	FDL	VIEW		50 < L ≤ 100	±0.40