

	1	2	3	4	5	6	7	8																																											
A									A																																										
B									B																																										
C	Features: • 2 ~ 12 circuits available • Material:nylon 66 UL 94V-2 or UL 94V-0								C																																										
D	Dimensional Information (mm) <table><tr><th>Circuits</th><th>Dim. A</th><th>Dim. B</th><th>Circuits</th><th>Dim. A</th><th>Dim. B</th></tr><tr><td>2</td><td>4.20</td><td>9.6</td><td>8</td><td>29.40</td><td>34.8</td></tr><tr><td>3</td><td>8.40</td><td>13.8</td><td>9</td><td>33.60</td><td>39.0</td></tr><tr><td>4</td><td>12.60</td><td>18.0</td><td>10</td><td>37.80</td><td>43.2</td></tr><tr><td>5</td><td>16.80</td><td>22.2</td><td>11</td><td>42.00</td><td>47.4</td></tr><tr><td>6</td><td>21.00</td><td>26.4</td><td>12</td><td>46.20</td><td>51.6</td></tr><tr><td>7</td><td>25.20</td><td>30.6</td><td></td><td></td><td></td></tr></table>								Circuits	Dim. A	Dim. B	Circuits	Dim. A	Dim. B	2	4.20	9.6	8	29.40	34.8	3	8.40	13.8	9	33.60	39.0	4	12.60	18.0	10	37.80	43.2	5	16.80	22.2	11	42.00	47.4	6	21.00	26.4	12	46.20	51.6	7	25.20	30.6				D
Circuits	Dim. A	Dim. B	Circuits	Dim. A	Dim. B																																														
2	4.20	9.6	8	29.40	34.8																																														
3	8.40	13.8	9	33.60	39.0																																														
4	12.60	18.0	10	37.80	43.2																																														
5	16.80	22.2	11	42.00	47.4																																														
6	21.00	26.4	12	46.20	51.6																																														
7	25.20	30.6																																																	
E	Specification: • Current rating and wire size: <table><tr><th>Wire Size</th><th colspan="2">Circuits</th></tr><tr><th>AWG</th><th>2, 3</th><th>4 ~ 6</th></tr><tr><td># 16</td><td>9 A</td><td>8 A</td></tr><tr><td># 18</td><td>9 A</td><td>8 A</td></tr><tr><td># 20</td><td>7 A</td><td>6 A</td></tr><tr><td># 22</td><td>5 A</td><td>4 A</td></tr><tr><td># 24</td><td>4 A</td><td>3 A</td></tr><tr><td># 26</td><td>3 A</td><td>2 A</td></tr><tr><td># 28</td><td>2 A</td><td>1 A</td></tr></table>								Wire Size	Circuits		AWG	2, 3	4 ~ 6	# 16	9 A	8 A	# 18	9 A	8 A	# 20	7 A	6 A	# 22	5 A	4 A	# 24	4 A	3 A	# 26	3 A	2 A	# 28	2 A	1 A	E															
Wire Size	Circuits																																																		
AWG	2, 3	4 ~ 6																																																	
# 16	9 A	8 A																																																	
# 18	9 A	8 A																																																	
# 20	7 A	6 A																																																	
# 22	5 A	4 A																																																	
# 24	4 A	3 A																																																	
# 26	3 A	2 A																																																	
# 28	2 A	1 A																																																	
F	Ordering Information <table><tr><th>Part No.</th><th>Material</th></tr><tr><td>H5150-XXPSW000R</td><td>UL 94V-2</td></tr><tr><td>H5150-XXPSW001R</td><td>UL 94V-0</td></tr></table> && xx = 02 ~ 12								Part No.	Material	H5150-XXPSW000R	UL 94V-2	H5150-XXPSW001R	UL 94V-0	F																																				
Part No.	Material																																																		
H5150-XXPSW000R	UL 94V-2																																																		
H5150-XXPSW001R	UL 94V-0																																																		
G									G																																										
H	RoHS Compliant APPD. 核准 DWG. 製圖 Hedy DATE 制表日 2020/07/31 SCALE 比例 UNIT 單位 PAGE 張數 1 / 1 參考 MM B HSM 玄茂科技股份有限公司 HSUAN MAO TECHNOLOGY CO., LTD. TOLERANCE .000 ± 0.08 (mm) .00 ± 0.25 (mm) .0 ± 0.4 (mm) SIZE. 紙張尺寸 A 4 REV. 版次 B PART NAME 品名 MINI FIT 4.2mm MALE HOUSING 1XXXP WHITE ROHS PART NO. 料號 H5150-XXPSW00XR								H																																										
	1	2	3	4	5	6	7	8																																											