




DIN 85 A

~ISO 1580

4.8

Standard withdrawn



BN 20243

Slotted pan head machine screws

Steel 4.8

zinc plated with thick layer passivation

- ~UNI 6108
- ~ČSN 021137

 [3D Cadenas](#)
 All lengths fully threaded

M2,5: in accordance with ISO 1580

Article#	d ₁	d ₂	k max.	n	t min.	L
3370980	M2,5	5	1,5	0,6	0,6	5
3370981						6
3370982						8
3370975						10
3370976						12
3370977						16
3370978						20
3370979						30
3370991	M3	6	1,8	0,8	0,7	4
3370993						5
3370994						6
3370995						8
3370983						10
3370984						12
3370985						(14)
3370986						16
3370987						20
3370988						25
3370990						30
3370992						40
3371005	M4	8	2,4	1,2	1	5
3371007						6
3371008						8
3370997						10
3370998						12
3370999						16

M2,5: in accordance with ISO 1580

Article#	d ₁	d ₂	k max.	n	t min.	L
3371000	M4	8	2,4	1,2	1	20
3371001						25
3371002						30
3371003						35
3371004						40
3371006						50
3371017	M5	10	3	1,2	1,2	8
3371009						10
3371010						12
3371011						(14)
3371012						16
3371013						20
3371014						25
3371015						45
3371025	M6	12	3,6	1,6	1,4	8
3371018						10
3371019						12
3371020						16
3371021						20
3371022						25
3371023						30
3371024						35