


EXIOS +A2F brass blank

Item number 1608900050



Technical data

Material	Brass
Seal	VMQ (silicone)
Material o-ring	VMQ (silicone)
Clamping insert	Polyamide 6
Protection class	IP 68 – 5 bar, IP 66, IP 68
Ex-protection level	Class I Div 2 Groups A,B,C,D, Class II Div 1 Groups E,F,G , II 1D Ex ta IIIC Da, II 2G Ex eb IIC Gb
Temperature range	-60°C to +105°C
Variant	Metric
External thread (AG)	M90 x 2,0
Size	75
A1	62 – 78 mm
Thread length (GL)	20 mm
Height (H)	76,2 mm
Wrench size (SW1/SW2)	95/95 mm



ATEX

ABS



Dimensions and specifications may be changed without prior notice

www.hummel.com

EXIOS +A2F brass blank

Item number 1608900050

D	107 mm
---	--------

Tightening torque	135 Nm
-------------------	--------



ATEX

ABS



Dimensions and specifications may be changed without prior notice

www.hummel.com

EXIOS +A2F brass blank

Item number 1608900050

Commercial data

Packaging Unit	1
EAN code	4033878429235
Weight	1.56108 kg
ETIM 7	EC000441
eCl@ss 10.1	27-14-44-34

Note:



Dimensions and specifications may be changed without prior notice



www.hummel.com