5SDA 27F2002

Old part no. DA 808-2700-20

Avalanche Diode

Properties

- low on-state voltage
- avalanche reverse characteristics
- high operational reliability
- suitable for parallel operation

Key Parameters

V_{RRM}	=	2 000	V
I_{FAVm}	=	2 700	A
I_{FSM}	=	31 000	A
V_{TO}	=	0.790	V
r_T	=	0.090	mΩ

Types

	V_{RRM}
5SDA 27F2002	**2 000 V**
Conditions:	T_j = -40 ÷ 160 °C, half sine waveform, f = 50 Hz

Mechanical Data

F_m	**Mounting force**	22 ± 2	kN
m	**Weight**	0.46	kg
D_S	**Surface creepage d stance**	30	mm
D_a	**Air strike distance**	20.5	mm



Fig. 1 Case

ABB s.r.o.
Novodvorska 1768/138a, 142 21 Praha 4, Czech Republic
tel.: +420 261 306 250, http://www.abb.com/semiconductors

Maximum Ratings			Maximum Limits	Unit
V_{RRM}	**Repetitive peak reverse voltage** *T_j = -40 ÷ 160 °C*		**2 000**	**V**
I_{FAVm}	**Average forward current** *T_c = 85 °C*		**2 700**	**A**
I_{FRMS}	**RMS forward current** *T_c = 85 °C*		**4 240**	**A**
I_{RRM}	**Repetitive reverse current** *$V_R = V_{RRM}$*		**50**	**mA**
I_{FSM}	**Non repetitive peak surge current** *V_R = 0 V, half sine pulse*	*t_p = 8.3 ms*	**33 100**	**A**
		t_p = 10 ms	**31 000**	**A**
I^2t	**Limiting load integral** *V_R = 0 V, half sine pulse*	*t_p = 8.3 ms*	**4 550 000**	**A^2s**
		t_p = 10 ms	**4 805 000**	**A^2s**
P_{RSM}	**Maximum avalanche power dissipation** *rectangular pulse 20 µs*		**100**	**kW**
T_{jmin} **-** T_{jmax}	**Operating temperature range**		**-40 ÷ 160**	**°C**
T_{STG}	**Storage temperature range**		**-40 ÷ 160**	**°C**

Unless otherwise specified T_j = 160 °C

Characteristics		Value			Unit
		min	typ	max	
V_{T0}	**Threshold voltage**			**0.790**	**V**
r_T	**Forward slope resistance** *I_F = 2000 ÷ 6000 A*			**0.090**	**mΩ**
V_{FM}	**Maximum forward voltage** *I_{FM} = 4 000 A*			**1.200**	**V**
Q_{rr}	**Recovered charge** *V_R = 100 V, I_{FM} = 2 000 A, di_F/dt = -5 A/µs*		**1 900**		**µC**

Unless otherwise specified T_j = 160 °C

Thermal Parameters			Value	Unit
R_{thjc}	**Thermal resistance junction to case**	*double side cooling*	**20**	**K/kW**
		anode side cooling	**34**	
		cathode side cooling	**48**	
R_{thch}	**Thermal resistance case to heatsink**	*double side cooling*	**5**	**K/kW**
		single side cooling	**10**	

Transient Thermal Impedance

Analytical function for transient thermal impedance

$$Z_{thjc} = \sum_{i=1}^{4} R_i (1 - \exp(-t / \tau_i))$$

Conditions:

F_m = 22 ± 2 kN, Double side cooled

i	1	2	3	4
R_i(K/kW)	11.83	4.26	1.63	2.28
τ_i (s)	0.432	0.071	0.01	0.0054



Fig. 2 Transient thermal impedance junction to case



Fig. 3 Maximum forward voltage drop characteristics



Fig. 4 Surge forward current vs. pulse length, half sine wave, single pulse, V_R = 0 V, T_j = T_{jmax}



Fig. 5 Forward power loss vs. average forward current, sine waveform, f = 50 Hz, T = 1/f



Fig. 6 Forward power loss vs. average forward current, square waveform, f = 50 Hz, T = 1/f



Fig. 7 Max. case temperature vs. aver. forward current, sine waveform, f = 50 Hz, T = 1/f



Fig. 8 Max.case temperature vs. aver. forward current, square waveform, f = 50 Hz, T = 1/f

Notes: