





Characteristics



General Characteristics	Standard	Value
number of contacts		2
termination technique		crimp
wire gauge		10 mm ² - 35 mm ² AWG 8 - AWG 2
max. insulation diameter		13 mm
flammability	UL 94	V-0
Electrical Characteristics	Standard	Value
rated voltage	IEC 60664-1	1000 V (UL/CSA: 600 V)
pollution degree	IEC 60664-1	3
installation (overvoltage) category	IEC 60664-1	3
material group	IEC 60664-1	1
rated impulse withstand voltage	IEC 60664-1	8 kV
rated current T _{amb} = 40 °C		100 A
current carrying capacity	IEC 60512-5-2	see derating curve
contact resistance	IEC 60512-2-1	≤ 5 mΩ
insulation resistance	IEC 60512-3-1	≥ 10 ¹⁰ Ω
Climatical Characteristics	Standard	Value
climatic category	IEC 60068-1	40 / 125 / 10
upper temperature	IEC 60512-11-9	+125 °C
lower temperature	IEC 60512-11-10	-40 °C
Mechanical Characteristics	Standard	Value
mechanical operation	IEC 60512-9-1	≥500 mating cycles
Materials	Standard	Value
insert		PA-GF
contacts		CuZn (brass)
contact plating		Ag (silver)
color		black

Gewicht (errechnet) / Calc WT: 17,8 g				Zul. Abw./Tolerances : ISO 2768-m		Maßstab / Scale : 1:1		A3		
Prüfmaß / Testdimension						CUSTOMER DRAWING				
Teileindex / Partindexnumber:										
Bagatelle change:										
				Gez.	09.10.2015	Stiftmodul 2-Pol pinmodule 2 pole				
				Drawn	PWOELFFLE					
				Status	Released					
				Gepr.	08.09.2017					
				Checked	MGRIMM	M C146 10A002 600 15				
04	201700257	30.08.2017	PWÖLF							
03	201600736	27.10.2016	PWÖLF							
02	201600377	07.06.2016	PWÖLF							
01	201500704	09.10.2015	PWÖLF							
				Amphenol Tuchel Industrial GmbH		Blatt / Sheet				
						1				
						1 E				
Index	Änderung / Description		Datum / Date	Name	Ers. f. / Replacement for: M-C146 10A002 100 15 Rev.02					

Alle technischen Daten wurden unter Laborbedingungen ermittelt und können im Praxisbetrieb abweichen.
Es handelt sich bei den Angaben weder um Beschaffenheits- noch um Haltbarkeitsgarantien.
All technical data have been measured in a laboratory environment and can be different during practical usage of the product. Any product information is for descriptive usage only and not legally binding; particularly the information does not constitute or provide any legal guarantees ("Beschaffenheitsgarantie" or "Haltbarkeitsgarantie").